



## 108356312 | FLEXIMAX PANEL

**FlexiMAX U/UTP High Density Patch Panel**

### Dimensions

Depth	105.92 mm   4.17 in
Height	43.69 mm   1.72 in
Width	482.60 mm   19.00 in

### Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cUL   UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

### General Specifications

Brand	SYSTIMAX®
Product Type	Panel
Total Ports, quantity	24
Color	Black
Package, quantity	1
Rack Type	EIA 19 in
Rack Units	1

### Mechanical Specifications

Material Type	High-impact, flame retardant, thermoplastic   Powder-coated steel
---------------	---

### Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

