


Part Number.....MMPD615HV

Made in the USA ..... No  
 Mounting..... H/V  
 AC Rating Volts..... 120  
 AC Rating Amps..... 12  
 AC Rating Watts..... 1440  
 AC Rating Frequency-Hz..... 50/60 HZ  
 Circuit Breaker..... 15A  
 Power LED..... Green  
 On/Off Switch..... None  
 Over Current Protection..... CB  
 Power Cable AWG..... 14/3 SJT  
 Power Cable Length..... 15'  
 Plug Type..... NEMA 5-15P  
 Receptacle Type..... NEMA 5-15R  
 Receptacle Style..... Duplex  
 Receptacle Quantity..... 6  
 Max.Output per Powerstrip..... 12 Amp  
 Joule Rating..... N/A  
 UL Rating..... 60950-1  
 Clamping Level..... N/A  
 Response Time..... N/A  
 Max.Surge Current..... N/A  
 EMI/RFI Noise Reduction..... N/A  
 Surge Indicator Red LED..... N/A  
 Connected Equipment Warranty..... N/A  
 Product Warranty-GLCC.....  
 Certification/Agency Approvals..... UL, CUL  
 Unit Weight lbs..... 4.2



INTERPRET DRAWING PER ASME Y14.5M-1994 DIMENSIONAL LIMITS APPLY AFTER APPLICATION OF FINISH DRAWING NOT TO SCALE TOLERANCE UNLESS OTHERWISE NOTED: ANGULAR +/- 1 .XXX +/- .010 .XX +/- .015 .X FOR REF ONLY		<b>NOTICE:</b> Use of this document is subject to a confidentiality and nondisclosure agreement with Great Lakes Case & Cabinet Co., Inc. (GLCC) and may not be reproduced, disclosed or utilized in whole or in part without prior written authorization from GLCC.		PART NUMBER: <b>7219 Power Strip</b> QTY PER UNIT: 1 MATERIAL TYPE: MATERIAL GAUGE: FINISH: SEE NOTES DRAWN: MZ CHECKED & APP: WSS DATE: 1/11/2011 DATE: 1/11/2011		TITLE: <b>GREAT LAKES CASE &amp; CABINET CO., INC.</b> P.O. BOX 551 EDINBORO, PA 16412 PHONE (814) 734-7303 FAX (814) 734-3907 E-MAIL glcc@greatlakes.com	
THIRD ANGLE PROJECTION		DWG NO: <b>1013250</b>		REV: 0		SHEET: 1 OF 1	