



MODEL	A	B	C	D	DEPTH
PB2	4.5	2.75	.625	1.375	3
NOTE: FASTENERS NOT SHOWN ALL DIMENSIONS IN INCHES.					

## PUSH BUTTON - MODEL PB2

### Features

- SPDT 10 amp contacts (DPDT available, see How to Order section)
- Large 2" diagonal flush button
- Momentary operation
- 12/24 VDC LED button illumination and a red LED (illuminated version only)
- Stainless steel single gang plate (back box included on illuminated versions)



### Operating Temperatures 0 to 43C [32 to 110F]

### Options

- **H** – Handicap
- **E** – Economy non-illuminated
- **2** - DPDT

## PUSH BUTTON - MODEL PB2 (cont'd)

### How to Order

<u>Part #</u>	<u>Description</u>
<b>PB2</b>	Push Button 2" Square Mom. SPDT Single Gang Illuminated
<b>PB2H</b>	Push Button 2" Square Mom. SPDT Handicap Illuminated
<b>PB2E</b>	Push Button 2" Square Mom. SPDT Single Gang
<b>PB2EH</b>	Push Button 2" Square Mom. SPDT Handicap
<b>PB2-2</b>	Push Button 2" Square Mom. DPDT Single Gang Illuminated

### Architectural Specifications

- A. The Push Button shall be produced by an ISO 9001 certified manufacturer.
- B. The Push Button shall be a 2" by 2" industrial grade button with protective cowling.
- C. The Button shall be labeled 'EXIT" and shall be green back lit using an incandescent bulb. A separate red LED shall be provided as an additional indicator.
- D. The LED's shall operate on 12 or 24 VDC (field selectable).
- E. The switch shall be SPDT and rated at 10 Amps at 12 or 24 VDC.
- F. The push button shall be mounted on a Stainless Steel - 630/US32D single gang faceplate.
- G. The switch shall be available in momentary action in both illuminated and non-illuminated versions.