

CS50™/CS55™

Plantronics CS50/55 wireless headset systems combine the clarity of traditional corded technology with the mobility of wireless, so employees can move around the office to wherever business takes them—without interrupting or missing a call.

Continuing our tradition as a technology leader, Plantronics presents CS55 as the first headset in the United States to implement 1.9GHz voice-dedicated wireless technology, while the CS50 operates at a frequency of 900 MHz.

CS50/CS55 Benefits

- Mobile multi-tasking—conferring with colleagues, walking to the printer, pouring a cup of coffee—need not interrupt important calls up to 300 feet from a desk phone.
- The CS50/CS55 gives workers 10 hours of unencumbered talk time and the option of remote answering*, so they never miss calls when away from the workstation.
- An extended boom and noise-canceling microphone filter out background sounds for heightened speech clarity.
- Delivers the audio quality of corded handsets—without the tether.
- The clear audio leader: the CS55 is the first headset in the U.S. to offer voice-dedicated 1.9 GHz DECT wireless technology.
- Employees can answer, end, and mute calls on the headset with the touch of a button.



Backed by Plantronics global service and support



Convertible Headset:
Over-the-head style... converts to... Over-the-ear style

*Requires HL10 Handset Lifter sold separately.

For more information about the CS50, CS55 or other Plantronics products, please visit our Web site at: plantronics.com

Tel: 866-544-4660 (U.S. And Canada)
831-458-7700 (Outside U.S.)



Volume up/down and mute

Charging cradle with IntelliStand™ feature

Power, online, and charge indicator lights

Call answer/end

Online indicator light

Noise-canceling microphone



The HL10 Handset Lifter adds the convenience of one touch answering and ending calls while away from your desk by automatically lifting your deskphone handset when a call comes in.

Talk Time:	Up to 8 hours
Standby Time:	Up to 70 hours
Range:	Up to 300 ft
Operating Frequency:	CS50: 900 MHz digital, CS55: DECT 6.0 (1.9 GHz)
Security/Privacy:	Digitally encrypted
Headset Microphone:	Noise-canceling
Headset Weight:	26 g
Headset Controls:	Volume, Mute, Call Answer/End
Battery Type:	Lithium Ion Polymer
Battery Recharge Time:	1.5 hours (80%) / 3 hours (100%)
Compatibility:	Most office or PBX-based telephones
Wearing Styles:	Convertible: over-the-ear, over-the-head, behind-the-head (with accessory neckband)
Limited Warranty:	1 year



© 2010 Plantronics, Inc. All rights reserved. Plantronics, the logo design, CS50, CS55, HL10, IntelliStand, and Sound Innovation are trademarks or registered trademarks of Plantronics, Inc. DECT is a trademark of ETSI. Published Sept 2010.