

www.GESecurity.com

2202 Series Overhead Door Magnetic Contacts


Surface/floor mount contacts with armored cable

Overview

The GE Security 2202 Series overhead door magnetic contact is for use in the rigorous environments of commercial and industrial installations.

The floor mount units are constructed with a low profile heavy cast aluminum housing. The reed switch assembly is fully encased in GE Security's exclusive polyurethane potting material to prevent damage due to moisture or humidity. A wide operating gap distance of up to 3 inches makes installation easy and helps prevent false alarms caused by door movement or damaged and loose fitting doors.

The 2202 Series is available with a universal style magnet that allows for greater installation flexibility.



Standard Features

- Wide 3-inch operating gap
- Fully sealed switch
- Form C unit available
- Mounting hardwire included



2202 Series Overhead Door Magnetic Contacts

Surface/floor mount contacts with armored cable

Specifications

Electrical, 2202

· Voltage: 100 VAC/DC max.

· Current: 0.5 A max.

· Power: 7.5 W max.

Electrical, 2204

· Voltage: 30 VAC/DC max.

· Current: 0.25 A max.

· Power: 3.0 W max.

Features, 2202

Loop type: Closed

• Electrical configuration: Normally open

· Gap distance: Up to 3 in.

· Lead type: 18 in. flexible stainless steel cable

Features, 2204

· Loop type: Open or closed

· Electrical configuration: SPDT

· Gap distance: Up to 3 in.

· Lead type: 18 in. flexible stainless steel cable

Lead colors: Black - common; white - closed loop (N.O.); red - open loop (N.C.)


Physical

- Dimensions, 2202A (LxWxD): 3.50 x 1.50 x 1.50 in. (89 x 38 x 38 mm)
- Dimensions, 2202AU and 2204AU (LxWxD): 3.125 x 2.125 x 0.81 in. (79 x 54 x 21 mm)
- · Construction: Cast aluminum
- · Color: Aluminum

Regulatory

· C-UL-US

Related Diagram



Ordering Information

2202A-L Floor-mount magnetic contact for overhead doors, aluminum housing, 3 in. gap size, closed loop, includes

18 in. stainless steel armored cable

Floor-mount magnetic contact for overhead doors, universal magnet, 3 in. gap size, closed loop, includes 18 2202AU-L

in. stainless steel armored cable

2204A-L Floor-mount magnetic contact for overhead doors,

aluminum housing, 3 in. gap size, SPDT, includes 18 in.

stainless steel armored cable

2204AU-L Floor-mount magnetic contact for overhead doors,

universal magnet, 3 in. gap size, SPDT, includes 18 in.

stainless steel armored cable



503-885-5700 888-GE-SECURITY (437-3287) faxback 800-483-2495 email info@gesecurity.com www.gesecurity.com

Asia tel 852-2907-8108 fax 852-2142-5063

tel +44-113-238-1668 fax +44-113-253-8121 Latin America

Europe

Australia tel +61-3-9259-4700 tel 305-267-4301 fax +61-3-9259-4799 fax 305-267-4300