

Flexible Conduits & Fittings

T&B Catalog Number: BVIDA-U150GT

UPC Number: 78620994959

Status: Active

Description:

PMAFIX black female thread adapter with UNEF threads and universal safety clip. Material - polyamide 6, thread size - 5/8 in. - 24, nominal width/ conduit size - 10. For use with AMP connectors.

Application

	For cable protection systems in a wide range of applications

Characteristics

	Very high impact resistance
	Suitable for the AMP connector series CPC
	Vibration proof connection to PMAFLEX conduits
	High conduit pull-out strength
	Easy installation, simply push the conduit in
	Can be easily re-opened with a screwdriver
	Very good chemical properties
	Free from halogens and cadmium
	Fits both conduit profiles, fine (T) and coarse (G)

General

Material	Polyamide 6
Color	Black
Thread Type	UNEF
Compatiable With	PMAFLEX, AMP Connector series CPC

Dimension Information

Fits to Conduit Size (NW)	10
Fits to Conduit Size (metric)	12
Fits to Conduit Size (inches)	5/16
Thread Size (UNEF)	5/8" - 24

Technical Information

Temperature Range-Continuous (Celsius)	-40 degree C to +105 degree C
Temperature-Short-Term (Celsius)	+160 degree C
Technical Data Sheet	Available on Website
Chemical Resistance Chart	Available on Website

Specifications

3dmodel	Available on Website

IP Ratings

IP Rating	IP 66 stat. / IP 54 dyn. On conduit side

Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	700
T&B Sold in UOM	Each
T&B Weight Per UOM	0.09 lbs. Each

Application Support

PMA Reference Guide	Available on Website

Prouduct Overview-PMAFIX Connectors	Available on Website
PMAFIX Connectors-Safety and Sealing Systems	Available on Website

Certifications

RoHS Compliance	Yes

Certifications



For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com