

## Flexible Conduits & Fittings

**T&B Catalog Number:** BVIDB-U267GT
**UPC Number:** 78620994976
**Status:** Active
**Description:**

PMAFIX black female thread adapter with UNEF threads and universal safety clip. Material - polyamide 6, thread size - 1-1/16 in. - 18, nominal width/conduit size - 17.

### Application

| | |
|---|---|
| | For cable protection systems in a wide range of applications |

### Characteristics

| | |
|---|---|
| | Very high impact resistance |
| | Vibration proof connection to PMAFLEX conduits |
| | Easy installation, simply push the conduit in |
| | High conduit pull-out strength |
| | Can be easily re-opened with a screwdriver |
| | Very good chemical properties |
| | Free from halogens and cadmium |
| | Fits both conduit profiles - fine (T) and coarse (G) |

### General

| | |
|---|---|
| Material | Polyamide 6 |
| Color | Black |
| Thread Type | UNEF |
| Compatiable With | PMAFLEX/ Souriau connector series UTG-6 / ITT Cannon Trident |

### Dimension Information

| | |
|---|---|
| Fits to Conduit Size (NW) | 17 |
| Fits to Conduit Size (metric) | 20 |
| Fits to Conduit Size (inches) | 1/2 |
| Thread Size (UNEF) | 1-1/16" - 18 |

### Technical Information

| | |
|---|---|
| Temperature Range-Continuous (Celsius) | -40 degree C to +105 degree C |
| Temperature-Short-Term (Celsius) | +160 degree C |
| Technical Data Sheet | Available on Website |
| Chemical Resistance Chart | Available on Website |

### Specifications

| | |
|---|---|
| 3dmodel | Available on Website |

### IP Ratings

| | |
|---|---|
| IP Rating | IP 68 stat. / IP 54 dyn. On conduit side |

### Packaging

| | |
|---|---|
| T&B Order Multiple | 50 |
| T&B Inner Pack | 50 |
| Package in Units | 300 |
| T&B Sold in UOM | Each |
| T&B Weight Per UOM | 0.02 lbs. Each |

### Application Support

| | |
|---|---|
| PMA Reference Guide | Available on Website |

| | |
|---|---|
| Prouduct Overview-PMAFIX Connectors | Available on Website |
| PMAFIX Connectors-Safety and Sealing Systems | Available on Website |

## Certifications

| | |
|---|---|
| RoHS Compliance | Yes |

## Certifications



**For further technical assistance, please contact us...**


Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com