



Split-Bolt
T&B Catalog Number:

1000M

UPC Number:

78378620021

Status:

Active

Description:

Type H - High Strength Split-Bolt Connector, Conductor Range for Equal Main and Tap 1000 kcmil-800 kcmil, Conductor Range for Min Tap with One Max Main 4/0 Str

Features

Bolt and nut of high-strength corrosion-resistant bronze alloy. Copper alloy pressure bar.

Standards

UL, CSA

Application

Splicing, tapping or terminating conductors in power and grounding electrical connection.

General

Style Type H

Wire Type Copper

Material Bronze Alloy

Color Metallic

Conductor Range for Equal Main and Tap 1000 kcmil-800 kcmil

Conductor Range Min. Tap with one Max. 4/0 Str.

Main

Dimension Information

A (inches) 2 1/4

B (inches) 1.185

C (inches) 2 17/32

D (inches) 4 1/32

Packaging

T&B Inner Pack 1

Package in Units 18

T&B Sold in UOM Each

T&B Weight Per UOM 2.6 lbs. Each

Notes

UL recognizes solid and stranded conductor configurations for sizes #8 and smaller and stranded configurations only for sizes #6 and larger.

Certifications

RoHS Compliance Yes

Certifications



File Nbr:

E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com