

Patch Cords

Category 5e

The UNC5 Patch Cord is a single-ended PS plug to unterminated over stranded cordage.

This equipment cord has a high performance with lower variability. It supports Ultrall and DataPipe solutions Category 5e solutions.

Applications:

- Patch and equipment cords

Meets/exceeds:

- Category 5e /Class D requirements of ISO/IEC IS11801, CENELEC EN50173 AND TIA/EIA 568B.2
- UL® Listed

Features:

- Supports to 1 Gb/s
- Consistently high performance
- Low variability
- Stranded conductors
- Performance exceeding the cordage requirements of TIA/EIA 568B.2 and ISO/IEC 11801
- Offered with or without translucent boots



Available in Blue, White and Gray colors and lengths of 1, 3, 5, 7, 10, 12, 15, 20, 25 and 50 feet. Additional colors and lengths are available upon request.

Specifications

Product	Length	Packaging	Color
UNC5-GY-1F-B	0.3 m (1 ft)	1 ea	Gray
UNC5-GY-3F-B	0.91 m (3 ft)	1 ea	Gray
UNC5-GY-5F-B	1.5 m (5 ft)	1 ea	Gray
UNC5-GY-7F-B	2.1 m (7 ft)	1 ea	Gray
UNC5-GY-10F-B	3 m (10 ft)	1 ea	Gray
UNC5-GY-12F-B	3.6 m (12 ft)	1 ea	Gray
UNC5-GY-15F-B	4.6 m (15 ft)	1 ea	Gray
UNC5-GY-20F-B	6 m (20 ft)	1 ea	Gray
UNC5-GY-25F-B	7.62 m (25 ft)	1 ea	Gray
UNC5-GY-50F-B	15.2 m (50 ft)	1 ea	Gray
UNC5-GY-1F-NB	0.3 m (1 ft)	1 ea	Gray
UNC5-GY-3F-NB	0.91 m (3 ft)	1 ea	Gray
UNC5-GY-5F-NB	1.5 m (5 ft)	1 ea	Gray
UNC5-GY-7F-NB	2.1 m (7 ft)	1 ea	Gray
UNC5-GY-10F-NB	3 m (10 ft)	1 ea	Gray
UNC5-GY-12F-NB	3.6 m (12 ft)	1 ea	Gray
UNC5-GY-15F-NB	4.6 m (15 ft)	1 ea	Gray
UNC5-GY-20F-NB	6 m (20 ft)	1 ea	Gray
UNC5-GY-25F-NB	7.62 m (25 ft)	1 ea	Gray
UNC5-GY-50F-NB	15.2 m (50 ft)	1 ea	Gray

Specifications

Product	Length	Packaging	Color
UNC5-WH-1F-B	0.3 m (1 ft)	1 ea	White
UNC5-WH-3F-B	0.91 m (3 ft)	1 ea	White
UNC5-WH-5F-B	1.5 m (5 ft)	1 ea	White
UNC5-WH-7F-B	2.1 m (7 ft)	1 ea	White
UNC5-WH-10F-B	3 m (10 ft)	1 ea	White
UNC5-WH-12F-B	3.6 m (12 ft)	1 ea	White
UNC5-WH-15F-B	4.6 m (15 ft)	1 ea	White
UNC5-WH-20F-B	6 m (20 ft)	1 ea	White
UNC5-WH-25F-B	7.62 m (25 ft)	1 ea	White
UNC5-WH-50F-B	15.2 m (50 ft)	1 ea	White
UNC5-WH-1F-NB	0.3 m (1 ft)	1 ea	White
UNC5-WH-3F-NB	0.91 m (3 ft)	1 ea	White
UNC5-WH-5F-NB	1.5 m (5 ft)	1 ea	White
UNC5-WH-7F-NB	2.1 m (7 ft)	1 ea	White
UNC5-WH-10F-NB	3 m (10 ft)	1 ea	White
UNC5-WH-12F-NB	3.6 m (12 ft)	1 ea	White
UNC5-WH-15F-NB	4.6 m (15 ft)	1 ea	White
UNC5-WH-20F-NB	6 m (20 ft)	1 ea	White
UNC5-WH-25F-NB	7.62 m (25 ft)	1 ea	White
UNC5-WH-50F-NB	15.2 m (50 ft)	1 ea	White

Patch Cords

Category 5e

Specifications

Product	Length	Packaging	Color
UNC5-BL-1F-B	0.3 m (1 ft)	1 ea	Blue
UNC5-BL-3F-B	0.91 m (3 ft)	1 ea	Blue
UNC5-BL-5F-B	1.5 m (5 ft)	1 ea	Blue
UNC5-BL-7F-B	2.1 m (7 ft)	1 ea	Blue
UNC5-BL-10F-B	3 m (10 ft)	1 ea	Blue
UNC5-BL-12F-B	3.6 m (12 ft)	1 ea	Blue
UNC5-BL-15F-B	4.6 m (15 ft)	1 ea	Blue
UNC5-BL-20F-B	6 m (20 ft)	1 ea	Blue
UNC5-BL-25F-B	7.62 m (25 ft)	1 ea	Blue
UNC5-BL-50F-B	15.2 m (50 ft)	1 ea	Blue
UNC5-BL-1F-NB	0.3 m (1 ft)	1 ea	Blue
UNC5-BL-3F-NB	0.91 m (3 ft)	1 ea	Blue
UNC5-BL-5F-NB	1.5 m (5 ft)	1 ea	Blue
UNC5-BL-7F-NB	2.1 m (7 ft)	1 ea	Blue
UNC5-BL-10F-NB	3 m (10 ft)	1 ea	Blue
UNC5-BL-12F-NB	3.6 m (12 ft)	1 ea	Blue
UNC5-BL-15F-NB	4.6 m (15 ft)	1 ea	Blue
UNC5-BL-20F-NB	6 m (20 ft)	1 ea	Blue
UNC5-BL-25F-NB	7.62 m (25 ft)	1 ea	Blue
UNC5-BL-50F-NB	15.2 m (50 ft)	1 ea	Blue

Specifications

Product	Length	Packaging	Color
UNC5-YL-1F-B	0.3 m (1 ft)	1 ea	Yellow
UNC5-YL-3F-B	0.91 m (3 ft)	1 ea	Yellow
UNC5-YL-5F-B	1.5 m (5 ft)	1 ea	Yellow
UNC5-YL-7F-B	2.1 m (7 ft)	1 ea	Yellow
UNC5-YL-10F-B	3 m (10 ft)	1 ea	Yellow
UNC5-YL-12F-B	3.6 m (12 ft)	1 ea	Yellow
UNC5-YL-15F-B	4.6 m (15 ft)	1 ea	Yellow
UNC5-YL-20F-B	6 m (20 ft)	1 ea	Yellow
UNC5-YL-25F-B	7.62 m (25 ft)	1 ea	Yellow
UNC5-YL-50F-B	15.2 m (50 ft)	1 ea	Yellow
UNC5-YL-1F-NB	0.3 m (1 ft)	1 ea	Yellow
UNC5-YL-3F-NB	0.91 m (3 ft)	1 ea	Yellow
UNC5-YL-5F-NB	1.5 m (5 ft)	1 ea	Yellow
UNC5-YL-7F-NB	2.1 m (7 ft)	1 ea	Yellow
UNC5-YL-10F-NB	3 m (10 ft)	1 ea	Yellow
UNC5-YL-12F-NB	3.6 m (12 ft)	1 ea	Yellow
UNC5-YL-15F-NB	4.6 m (15 ft)	1 ea	Yellow
UNC5-YL-20F-NB	6 m (20 ft)	1 ea	Yellow
UNC5-YL-25F-NB	7.62 m (25 ft)	1 ea	Yellow
UNC5-YL-50F-NB	15.2 m (50 ft)	1 ea	Yellow

Specifications

Product	Length	Packaging	Color
UNC5-GN-1F-B	0.3 m (1 ft)	1 ea	Green
UNC5-GN-3F-B	0.91 m (3 ft)	1 ea	Green
UNC5-GN-5F-B	1.5 m (5 ft)	1 ea	Green
UNC5-GN-7F-B	2.1 m (7 ft)	1 ea	Green
UNC5-GN-10F-B	3 m (10 ft)	1 ea	Green
UNC5-GN-12F-B	3.6 m (12 ft)	1 ea	Green
UNC5-GN-15F-B	4.6 m (15 ft)	1 ea	Green
UNC5-GN-20F-B	6 m (20 ft)	1 ea	Green
UNC5-GN-25F-B	7.62 m (25 ft)	1 ea	Green
UNC5-GN-50F-B	15.2 m (50 ft)	1 ea	Green
UNC5-GN-1F-NB	0.3 m (1 ft)	1 ea	Green
UNC5-GN-3F-NB	0.91 m (3 ft)	1 ea	Green
UNC5-GN-5F-NB	1.5 m (5 ft)	1 ea	Green
UNC5-GN-7F-NB	2.1 m (7 ft)	1 ea	Green
UNC5-GN-10F-NB	3 m (10 ft)	1 ea	Green
UNC5-GN-12F-NB	3.6 m (12 ft)	1 ea	Green
UNC5-GN-15F-NB	4.6 m (15 ft)	1 ea	Green
UNC5-GN-20F-NB	6 m (20 ft)	1 ea	Green
UNC5-GN-25F-NB	7.62 m (25 ft)	1 ea	Green
UNC5-GN-50F-NB	15.2 m (50 ft)	1 ea	Green

Specifications

Product	Length	Packaging	Color
UNC5-VL-1F-B	0.3 m (1 ft)	1 ea	Violet
UNC5-VL-3F-B	0.91 m (3 ft)	1 ea	Violet
UNC5-VL-5F-B	1.5 m (5 ft)	1 ea	Violet
UNC5-VL-7F-B	2.1 m (7 ft)	1 ea	Violet
UNC5-VL-10F-B	3 m (10 ft)	1 ea	Violet
UNC5-VL-12F-B	3.6 m (12 ft)	1 ea	Violet
UNC5-VL-15F-B	4.6 m (15 ft)	1 ea	Violet
UNC5-VL-20F-B	6 m (20 ft)	1 ea	Violet
UNC5-VL-25F-B	7.62 m (25 ft)	1 ea	Violet
UNC5-VL-50F-B	15.2 m (50 ft)	1 ea	Violet
UNC5-VL-1F-NB	0.3 m (1 ft)	1 ea	Violet
UNC5-VL-3F-NB	0.91 m (3 ft)	1 ea	Violet
UNC5-VL-5F-NB	1.5 m (5 ft)	1 ea	Violet
UNC5-VL-7F-NB	2.1 m (7 ft)	1 ea	Violet
UNC5-VL-10F-NB	3 m (10 ft)	1 ea	Violet
UNC5-VL-12F-NB	3.6 m (12 ft)	1 ea	Violet
UNC5-VL-15F-NB	4.6 m (15 ft)	1 ea	Violet
UNC5-VL-20F-NB	6 m (20 ft)	1 ea	Violet
UNC5-VL-25F-NB	7.62 m (25 ft)	1 ea	Violet
UNC5-VL-50F-NB	15.2 m (50 ft)	1 ea	Violet