

# Patch Panels



**Part Number:** OR-809004909

**Description:** 48-port voice/data panel, std density, mod to 110, 19" x 5.25"

Modular Quad Frame to 110 Patch Panel, 48 ports, active positions 3 and 4 of six-position RJ11 jack

## ■ Specifications

Performance Rating	Voice/Data
Panel or Accessory Type	Mod6 /110
Mod Jack Wiring	RJ11 (3,4)
Number of Ports	48
Critical Size	3 rack units
Color	Black with white print
Width	19 in (482.6 mm)
Depth	.125 in (3.175 mm)
Height	5.25 in (133.35 mm)
Cable Diameter Range	22-26 AWG
UL Listing No.	E131600
UL Standard	UL 1863
CUL Listing No.	E131600
CUL Standard	UL 1863
CSA Listing No.	LR 90894
CSA Standard	C22.2 No. 182.4-M90
FCC Standard	Part 68
Accessories	Color-Coded Cable Management Straps, Color-Coded Designation Shutters, Color-Coded Voice or Data Tabs, Modular Snap-in Dust Covers, Cable Ties, 110 Color-Coded Designation Strips, 110 Designation Kit

## ■ Construction

	Material	Finish/Plating
Panel	0.125" Aluminum	Painted black - texture, with white silkscreen
Six-position jack housing	ABS UL94V-0	
Modular jack contacts	Phosphor Bronze	50 micro inch gold or GTX
110 rear bracket	0.063" Aluminum	Painted black - no texture
25-pair base strip	Polycarbonate UL94V-0	
110C connecting blocks	Polycarbonate UL94V-0	
IDC contact	Phosphor Bronze	90/10 Tin lead plating
Designation cover	PVC	

## ■ Features

- Standard density design
- 110 termination

## ■ Benefits

- Increased room for cables
- Easy and reliable termination