

Patch Panels



Part Number: OR-808004920

Description: Mod 6/Telco Panel, 24-port quad / 3,4 / M50

Modular Six-Position Telco Patch Panel, quad frame, 24 ports, male 50-pin RJ21, active positions 3 and 4 of six-position jack

■ Specifications

Performance Rating	Voice/Data
Panel or Accessory Type	Mod6/ Telco M
Mod Jack Wiring	RJ11 (3,4)
Number of Ports	24
Critical Size	2 rack units
Color	Black with yellow print
Width	19 in (482.6 mm)
Depth	.125 in (3.175 mm)
Height	3.5 in (88.9 mm)
UL Listing No.	E131600
UL Standard	UL 1863
CUL Listing No.	E131600
CUL Standard	UL 1863
CSA Listing No.	LR 90894
CSA Standard	C22.2 No. 182.4-M90
FCC Standard	Part 68
Accessories	Modular Snap-in Dust Covers, Color-Coded Cable Management Straps, Color-Coded Designation Shutters, Color-Coded Voice or Data Tabs, Cable Ties

■ Construction

	Material	Finish/Plating
Panel	0.125" Aluminum	Painted black - texture, with white silkscreen
Six-position jack housing	ABS UL94V-0	
Modular jack contacts	Phosphor Bronze	50 micro inch gold or GTX
Hold-down bracket	Metal	
Hold-down strap	Hook and loop	
25-pair male connector housing	Polyphenylene	
25-pair male contacts	Copper	Gold over nickel
Strain relief	Polyphenylene	

■ Features

- Standard density design
- Modular 50-pin connection on back
- Supplied hook and loop connector ties

■ Benefits

- Increased room for cable management
- Allows quick connection
- Secures 50-pin connection