


Patch Panels



Part Number: OR-808004351

Description: Mod 8/Telco Panel, high density, 48 ports / T568B / F50

Modular Eight-Position Telco Patch Panel, high density, 48 ports, T568B, female 50-pin RJ21, 19" x 3.5"

■ Specifications

Performance Rating	Voice/Data
Panel or Accessory Type	Mod8/ Telco F
Mod Jack Wiring	T568B
Number of Ports	48
Critical Size	2 rack units
Color	Black with white print
Width	19 in (482.6 mm)
Depth	.125 in (3.175 mm)
Height	3.5 in (88.9 mm)
UL Listing No.	E131600
UL Standard	UL 1863
CUL Listing No.	E131600
CUL Standard	UL 1863
CSA Listing No.	LR 90894
CSA Standard	C22.2 No. 182.4-M90
FCC Standard	Part 68
Accessories	Modular Snap-in Dust Covers, Color-Coded Cable Management Straps, Color-Coded Designation Shutters, Color-Coded Voice or Data Tabs, Cable Ties

■ Construction

	Material	Finish/Plating
Panel	0.125" Aluminum	Painted black - texture, with white silkscreen
Eight-position jack housing	ABS UL94V-0	
Modular jack contacts	Phosphor Bronze	50 micro inch gold or GTX
Hold-down bracket	Metal	
Hold-down strap	Hook and loop	
25-pair female connector housing	Polyphenylene	
25-pair female contacts	Copper	Gold over nickel
Strain relief	Polyphenylene	

■ Features

- High density design
- Modular 50-pin connection on back
- Supplied hook and loop connector ties

■ Benefits

- Maximum use of rack space
- Allows quick connection
- Secures 50-pin connection