

TrueNet®

Category 6 KM8 Modular Punchdown Jacks



An integral part of the TrueNet® channel solution designed in conjunction with other TrueNet Category 6 components and cable, the ADC KM8 jack is a key element to the zero bit-error network performance warranty. These modular jacks can be used in any of ADC's modular plug-and-play station outlets and patch panels.

Features:

- TrueNet impedance matched jacks guarantee maximum throughput
- Exceeds TIA/EIA Category 6 requirements
- Forty-five degree silver-plated IDCs provide secure, reliable gas-tight connections
- Compatible with any TrueNet modular faceplate, modular furniture faceplate, surface box and modular patch panel
- Accepts either a KRONE® or 110 tool for wire termination for punchdown jack
- Universal A/B wiring label
- UL 1863 listed and Category 6 performance verified

SPEC SHEET



www.adc.com • +1-952-938-8080 • 1-800-366-3891

Specifications

Operating Temperature Range:

-40° to 70 °C (-40° to 158 °F)

RJ Socket, 8 Positions, General Specification:

FCC Part 68.500 (IEC 603-7)

Transmission Performance and Reliability:

≥ EIA/TIA 568-B.2-1 Category 6

≥ ISO 11801 Class E Standard

≥ 750 (IEC/EN 60603-7)

Number of Plug Insertion Cycles:**LSA-PLUS® Insulation Displacement****Wire Diameter Range for Solid and Stranded Copper Conductors:**

22-24 AWG

0.50 mm to 0.65 mm (0.016" to 0.025")

Wire Insulation Diameter Range (PE,PVC):

1.04 mm to 1.60 mm (0.041" to 0.063")

Contact Resistance:

≤ 1 mΩ typical

Contact Re-terminations:

≥ 200

Insulation Resistance at 40 °C (104 °F) and 93% RH:


≥ 500 MΩ (IEC 512-2-3a)

Safety Rating:


UL 1863

Flammability Rating:

UL 94 V-0



ADC's modular jacks and connectors may be used in all TrueNet modular faceplates, surface boxes, patch panels as well as any platform with a port opening of 14.9 mm x 19.2 mm (.585" x .757") with a plate thickness from 1.2 mm x 1.5 mm (.048" to .060".)



Ordering Information

Description	Catalog Number
KM8 RJ45 modular punchdown jack <i>Quantity: 1</i>	6830 1 830-XX*

*Replace XX with:

01 = White	07 = Green
02 = Ivory	08 = Yellow
03 = Gray	09 = Purple
04 = Black	10 = Orange
05 = Red	
06 = Blue	

SPEC SHEET

KRONE® is a registered trademark of ADC Telecommunications, Inc.

**Web Site: www.adc.com**

From North America, Call Toll Free: 1-800-366-3891 • Outside of North America: +1-952-938-8080
Fax: +1-952-917-3237 • For a listing of ADC's global sales office locations, please refer to our web site.

ADC Telecommunications, Inc., P.O. Box 1101, Minneapolis, Minnesota USA 55440-1101
Specifications published here are current as of the date of publication of this document. Because we are continuously improving our products, ADC reserves the right to change specifications without prior notice. At any time, you may verify product specifications by contacting our headquarters office in Minneapolis. ADC Telecommunications, Inc. views its patent portfolio as an important corporate asset and vigorously enforces its patents. Products or features contained herein may be covered by one or more U.S. or foreign patents. An Equal Opportunity Employer

1324771 6/05 Original © 2005 ADC Telecommunications, Inc. All Rights Reserved