


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	BUNDLE DIA.		A	B	C	MIN. LOOP ** TENSILE lbs. (N)	APPROXIMATE WEIGHT lbs/10 ROLLS (g)
	MIN. in (mm)	MAX. in (mm)					
* HLM-15R	.25 (6.4)	VARIOUS	.100 (2.5)	.180 (4572)	.330 (8.4)	.18 (80)	.55 (251)




ILLUSTRATION 'A'

NOTES:

- * 1) PACKAGED IN 15 FT. ROLLS. (SEE ILLUSTRATION 'A')
- ** 2) MINIMUM 2" OVERLAP REQUIRED TO ACHIEVE LOOP TENSILE RATING.
- 3) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR OPTIONAL COLORS.

										DIMENSIONS IN PARENTHESIS ARE IN METRIC UNITS				
										SS_27052_02.PRT				
										PANDUIT CORP. TINLEY PARK, ILLINOIS				
										TAK-TY CABLE TIE CONTINUOUS 15FT. ROLL HLM SERIES				
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .035(.89mm) (.XX) ± ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.		
										DRAWN BY KET	MAT'L:		SCALE NONE	
3	04/12/06	FAB		ADDED WEIGHTS TO DRAWING		27052	3			DATE 08-20-96	POLYETHYLENE HOOK/ NYLON KNIT LOOP		DRAWING NO. SS-27052	DWG A SIZE
REV	DATE	BY	CHK	DESCRIPTION		ECN	-	R	CUST	SUP	CHK'D HVP			