

| PANDUIT PART NO. | BUNDLE DIA. | | A in (mm) | B in (mm) | C in (mm) | D in (mm) | COLOR | UL LISTED * RATE LOAD lbs. (N) |
|---------------------|-----------------|-----------------|---------------|---------------|----------------|--------------|--------|--------------------------------------|
| | MIN. in (mm) | MAX. in (mm) | | | | | | |
| HLSP1.5S-X0 | .25 (6.4) | 1.5 (38.1) | .100 (2.5) | 6.0 (152) | .750 (19.1) | 2.8 (71) | BLACK | 18 (80) |
| HLSP1.5S-X12 | .25 (6.4) | 1.5 (38.1) | .100 (2.5) | 6.0 (152) | .750 (19.1) | 2.8 (71) | MAROON | 50 (222) |
| HLSP3S-X0 | .25 (6.4) | 3.2 (81.3) | .100 (2.5) | 12.0 (305) | .750 (19.1) | 3.6 (91) | BLACK | 18 (80) |
| HLSP3S-X12 | .25 (6.4) | 3.2 (81.3) | .100 (2.5) | 12.0 (305) | .750 (19.1) | 3.6 (91) | MAROON | 50 (222) |
| HLSP5S-X0 | .25 (6.4) | 5.0 (127) | .100 (2.5) | 18.0 (457) | .750 (19.1) | 4.5 (114) | BLACK | 18 (80) |
| HLSP5S-X12 | .25 (6.4) | 5.0 (127) | .100 (2.5) | 18.0 (457) | .750 (19.1) | 4.5 (114) | MAROON | 50 (222) |




ILLUSTRATION "A"

NOTES:

- 1) ALL LENGTHS PACKED IN ROLL FORM. (SEE ILLUSTRATION "A")
- * 2) MINIMUM 2" (50.8 mm) OVERLAP REQUIRED TO ACHIEVE UL LISTED RATED LOAD. (1.5 IN² OR 968 mm²)
- 3) HSLP TIES AVAILABLE IN BLACK AND MAROON ONLY.
- 4) SUITABLE FOR USE IN AIR HANDLING SPACES PER NEC SEC. 300-22 (C) AND (D).

PANDUIT CORP. TINLEY PARK, ILLINOIS

TAK-TY™ HOOK & LOOP CABLE TIES
HLSP SERIES
FLAMMABILITY RATING: UL 94-V2

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± (.XXX) ± .030
(.XX) ± .125 ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
K. TROST

| | |
|--------|--|
| MAT'L: | POLYPROPYLENE HOOK/ NYLON KNIT LOOP |
|--------|--|

| | |
|-------|------|
| SCALE | NONE |
|-------|------|

DRAWING NO.

SS-27183

DWG
A
SIZE

| | | | | | | | | | |
|-----|---------|------|-----|---|-------|-----|------|-----|--|
| | | | | | | | | | |
| | | | | | | | | | |
| | | | | | | | | | |
| | | | | | | | | | |
| | | | | | | | | | |
| --- | ---- | --- | | TO 2", WAS 1" REVISED NOTE # 2 MIN. OVERLAP | ---- | --- | | | |
| --- | ---- | --- | | MATERIAL POLYPROPYLENE WAS POLYETHYLENE | ---- | --- | | | |
| 2 | 6/20/02 | JABO | | ADDED MAROON TIES, ADDED DIM. D ADDED COLOR COLUMN | 27183 | 2 | | | |
| REV | DATE | BY | CHK | DESCRIPTION | ECN | - R | CUST | SUP | |