


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	MIN. LOOP * TENSILE lbs. (N)	CROSS SECTION	APPROXIMATE WEIGHT lbs/100 PIECES (g)
	MIN. in (mm)	MAX. in (mm)								
HLT21	.25 (6.4)	1.91 (48.5)	.100 (2.5)	.50 (12.7)	1.50 (38.1)	1.00 (25.4)	8.0 (203)	40 (178)	INTERMEDIATE	.48 (218)
HLT31	.25 (6.4)	3.18 (80.6)	.100 (2.5)	.50 (12.7)	1.50 (38.1)	1.00 (25.4)	12.0 (305)	40 (178)	INTERMEDIATE	.65 (295)

NOTES:

- 1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.
- * 2) MINIMUM 2" OVERLAP REQUIRED TO ACHIEVE LOOP TENSILE RATING.

CAD FILENAME/LAYERS										
DIMENSIONS IN PARENTHESIS ARE IN METRIC UNITS										
SS_26938_06.PRT										
PANDUIT CORP. TINLEY PARK, ILLINOIS										
TAK-TY™ HOOK & LOOP CABLE TIES HLT SERIES										
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .030 (.XX) ± .125 ANGLES ±								UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.		
6	1/13/06	ERW		ADDED APPROX. WEIGHT PER 100 PIECES	26938	6		DRAWN BY KET	MAT'L:	SCALE NONE
5	5/3/05	ERW	JVL	REMOVED OVAL SLOT DIMENSION TO BE CONSISTENT WITH OTHER CUSTOMER DRAWINGS	26938	5	JVL	DATE 11/28/94	POLYETHYLENE HOOK/ NYLON KNIT LOOP	DRAWING NO. SS-26938
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	CHK'D HVP	DWG SIZE A