


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	TIP STYLE	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)										
PLT.6SM	.01 (.3)	.6 (15)	.030 (.76)	.070 (1.8)	.124 (3.1)	.095 (2.4)	.125 (3.2)	2.8 (71)	8 (36)	SUB-MINIATURE	CURVED	.02 (9.0)
PLT.7M	.03 (.8)	.68 (17)	.032 (.8)	.090 (2.3)	.148 (3.8)	.115 (2.9)	.180 (4.6)	3.1 (79)	18 (80)	MINIATURE	CURVED	.04 (16)
PLT1M	.06 (1.5)	.87 (22)	.043 (1.1)	.098 (2.5)	.169 (4.3)	.154 (3.9)	.180 (4.6)	3.9 (99)	18 (80)	MINIATURE	CURVED	.07 (32)
PLT1.5M	.06 (1.5)	1.25 (32)	.043 (1.1)	.098 (2.5)	.169 (4.3)	.154 (3.9)	.180 (4.6)	5.6 (142)	18 (80)	MINIATURE	CURVED	.10 (45)
PLT2M	.06 (1.5)	2.00 (51)	.043 (1.1)	.098 (2.5)	.169 (4.3)	.154 (3.9)	.180 (4.6)	8.0 (203)	18 (80)	MINIATURE	CURVED	.13 (59)
PLT1.5I	.06 (1.5)	1.38 (35)	.045 (1.1)	.142 (3.6)	.206 (5.2)	.180 (4.6)	.240 (6.1)	5.6 (142)	40 (178)	INTERMEDIATE	CURVED	.14 (64)
PLT2I	.06 (1.5)	2.00 (51)	.045 (1.1)	.142 (3.6)	.206 (5.2)	.180 (4.6)	.240 (6.1)	8.0 (203)	40 (178)	INTERMEDIATE	CURVED	.20 (91)
PLT2.5I	.06 (1.5)	2.50 (64)	.052 (1.3)	.145 (3.7)	.220 (5.6)	.180 (4.6)	.260 (6.6)	9.7 (246)	40 (178)	INTERMEDIATE	CURVED	.27 (122)

NOTES:

- 1) RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC.
- *2) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE & PART COLOR.

SS-5540_31.PRT

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

PANDUIT CORP. TINLEY PARK, ILLINOIS

PAN-TY CABLE TIES
PLT SERIES

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± (.XXX) ± .020 (.51)
(.XX) ± .02 (.5) ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	DRWN BY	MAT'L:	SCALE	DWG
31	9/9/04	ERW		CORRECTED METRIC CONVERSIONS	5540	31			CEW	NYLON 6.6	NONE	A
30	2/12/03	JABO		CORRECTED PLT2M/2I 2.00 BUNDLE DIA (mm) TO (51)	5540	30			DATE 12-27-84		SHEET 1	
									CHK'D HVP			