


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.*	MAT'L SUFFIX	RECOMMENDED FASTENER	'A'	'B'	'C'	'D'	'E'	'F'	'G' 'REF'	'H' 'REF'	'I' 'REF'	USE WITH THESE CABLE TIE CROSS SECTIONS	WEIGHT (g) lbs/100 pcs.
TM3S8	NONE -0 -30 -49	#8 (M4) SCREW	0.863 [21.9]	0.610 [15.5]	0.373 [9.4]	0.320 [8.1] ±.020 [0.5]	0.088 [2.2] ±.020 [0.5]	0.208 [5.3]	0.105 [2.7]	0.325	0.180	MINIATURE INTERMEDIATE STANDARD LT. HEAVY	0.369 [167.5]
TM3S10	NONE -0 -30	#10 (M5) SCREW							0.115 [2.9]	0.385	0.200		0.363 [165.0]
TM3S25	NONE -0 -30	1/4" (M6) SCREW	0.879 [22.3]	0.629 [16.0]	0.379 [9.6]			0.210 [5.3]	0.155 [3.9]	0.506	0.262		0.296 [134.5]
TM3S2510	-30 -39	#10 (M5) SCREW	0.873 [22.2]	0.620 [15.7]				0.212 [5.4]	0.120 [3.0]	0.480	0.200		0.321 [145.5]


NOTES:

- *1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
2. HOLE DIMENSIONS SHOULD ACCOMMODATE SPECIFIED RECOMMENDED FASTENER.


MAT'L SUFFIX	MATERIAL	COLOR
NONE	NYLON 6/6	NATURAL
-0	WEATHER RESISTANT NYLON	BLACK
-30	HEAT STABILIZED NYLON	
-39	HEAT STABILIZED NYLON	NATURAL
-49	IMPACT MODIFIED NYLON	



SEE NOTE 2



SECTION A - A



DIMENSIONS IN BRACKETS ARE METRIC [mm]	
CAD FILENAME/LAYERS G00239EN_PB_TM3S_11	
PANDUIT CORP. TINLEY PARK, ILLINOIS	
TM3S - TIE MOUNT	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±0.05 [1.3] (.XXX) ±0.010 [0.25] (.XX) ±0.02 [0.5] ANGLES ±5°	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.
DRAWN BY AJV	MAT'L: SEE TABLE
DATE 12/17/96	SCALE NONE
CHK'D	DRAWING NO. GB0239EN
	DWG A SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
11	4/16/07	DJSM		ADDED DECIMAL PLACE TO TABLE, REMOVED MATERIALS -69 AND -100	GB0239EN	11		
10	03/19/07	DJSM		ADDED TM3S2510, ADDED MATERIAL -39, CHANGED TOLERANCES	GB0239EN	10		