



Application

TrueNet® loose tube, indoor/outdoor, LSZH duct grade cables.

Specifications

- **Outer Sheath:** LSZH, UV stabilised for outdoor applications, black.
- Water blocked (IEC60794).
- **Sheath Thickness:** 1.5mm.
- **Fire Retardancy:** 2 – 24 cores IEC 60332-1.
- Glass fibre armour.
- Available with OM1, OM2, OM3 and OM3e grade glass.
- Hybrid multimode and singlemode OS1 options available.

Anixter Number	Vendor Number	Description
OM1		
370-500-6LS2-04	7023 3 220-04	4 fibre 62.5/125 μ m
370-500-6LS2-08	7023 3 220-08	8 fibre 62.5/125 μ m
370-500-6LS2-12	7023 3 220-12	12 fibre 62.5/125 μ m
370-500-6LS2-16	7023 3 220-16	16 fibre 62.5/125 μ m
370-500-6LS2-24	7023 3 220-24	24 fibre 62.5/125 μ m
OM2		
370-500-5LS2-04	7023 3 222-04	4 fibre 50/125 μ m
370-500-5LS2-08	7023 3 222-08	8 fibre 50/125 μ m
370-500-5LS2-12	7023 3 222-12	12 fibre 50/125 μ m
370-500-5LS2-16	7023 3 222-16	16 fibre 50/125 μ m
370-500-5LS2-24	7023 3 222-24	24 fibre 50/125 μ m
OM3		
370-500-5LS2OM3-04	7023 3 227-04	4 fibre 50/125 μ m
370-500-5LS2OM3-08	7023 3 227-08	8 fibre 50/125 μ m
370-500-5LS2OM3-12	7023 3 227-12	12 fibre 50/125 μ m
370-500-5LS2OM3-16	7023 3 227-16	16 fibre 50/125 μ m
370-500-5LS2OM3-24	7023 3 227-24	24 fibre 50/125 μ m