

Straight Joint Kits for Three Core Medium Voltage Cables

- Quick and easy to use, with no requirement for application of heat to effect the joint (no open flames).
- No special tools required.
- Long term reliability.
- Provides excellent insulating levels.
- One part joint body.
- UV stabilised.
- High track resistance and built in permittivity stress controlling material.
- Non-flammable (LSOH) and fungus resistant.
- Manufactured from silicone (hydrophobic material).
- Terminations recover to a uniform wall thickness.
- Joint kit includes copper mesh tape, mastic, Elaseed joint, 2 x "C" spanners, EPR tape, 2 x constant force springs, 2 x sealing pads, silicone grease, 7 litres of resin and instructions.

Straight Joint Kit Details	
Anixter Part Number	To Suit Three Core 11 kV Polymeric Cable
SJK-EJ-3XA-A-12	95 – 185sqmm
SJK-EJ-3XA-B-12	185 – 300sqmm
SJK-EJ-3XA-C-12	400sqmm