features and benefits |

One part number solution	For most common fiber counts
All-inclusive kit	Trays, seals and hardware in every kit
Easy component additions	Future expandability

Closure Options

UCAO-05-24

- Includes closure housing, strain-relief and sealing hardware for two cables plus two UCAO-ST-02 splice trays for a capacity of 24 single-fiber splices, 12 per tray
- Small, compact, easy re-enterability, in-line design with four 28 mm ports, two per side

A LANscape® Solutions Product

UCAO-05-24 (continued)

- Suitable for aerial, pole/wall and buried applications
- Expandability: Maximum splicing capacity of 60 single-fiber splices

SCF-4C18-01-36

- Includes 4 x 18-in canister closure housing, strainrelief and sealing hardware for two main cables, one drop and three SCF-ST-099 splice trays for a capacity of 36 single-fiber splices
- Expandability: Maximum splicing capacity of 72 single-fiber splices, three more splice trays
- Port count: Two express and three drop ports
- Suitable for aerial as well as direct-buried applications

(continued)





SCF-4C18-01-36 Fiber Splice Closure | Photo SHD46





Closure Options (continued) SCF-6C22-01-72

- Includes 6 x 22-in canister closure housing, strainrelief and sealing hardware for two main cables, one drop and six SCF-ST-099 splice trays for a capacity of 72 single-fiber splices
- Expandability: Maximum splicing capacity of 144 single-fiber splices, six more splice trays
- Port count: Two express and four drop ports
- Suitable for aerial as well as direct-buried applications

A LANscape® Solutions Product

SCF-6C28-01-144

- Includes 6 x 28-in canister closure housing, strainrelief and sealing hardware for two main cables, one drop and six SCF-ST-112 splice trays for a capacity of 144 single-fiber splices
- Expandability: Maximum splicing capacity of 288 single-fiber splices, six more splice trays
- Port count: Two express and four drop ports
- Suitable for aerial as well as direct-buried applications



SCF-6C22-01-72 Fiber Splice Closure | Photo SHD38




SCF-6C28-01-144 Fiber Splice Closure | Photo SHD44





ordering information |

Part Number Description UCAO-05-24 UCAO-05-24 UCAO Closure with two UCAO-ST-02 trays for 24-fiber applications UCAO Accessories UCAO-ST-02 UCAO Splice Tray, accommodates 12 heat-shrink splices **UCAO-AHD** Aerial Hanging Device for UCAO and UCA3-6 closures UCAO-BK1 Wall-/Pole-Mount Bracket for UCAO and UCA3-6 closures **UCAO-GND** Central Member Grounding Kit (10 pack) SCF-4C18-01-36 SCF-4C18-01-36 4 x 18-in Canister with three SCF-ST-099 trays for 36-fiber applications **4C18 Accessories SCF-ST-099** 12-Position Heat-Shrink 0.2-in Metal Tray for single fiber SCF-KT-6GND SFC-6 Ground Kit, fits all SCF closures (two per kit) SCF-KT-4CBL Add-a-Cable Kit for one port SCF-INST-BKT4 Table Installation Bracket for 4-in SCF SCF-6C22-01-72 / SCF-6C28-01-144 SCF-6C22-01-72 6 x 22-in Canister with six SCF-ST-099 trays for 72-fiber splices SCF-6C28-01-144 6 x 28-in Canister with six SCF-ST-112 trays for 144-fiber splices 6C Accessories SCF-ST-048 12-Position Heat-Shrink 0.2-in Metal Tray for single fiber **SCF-ST-112** 24-Position Heat-Shrink 0.2-in Metal Tray for single fiber SCF-KT-6GND SFC-6 Ground Kit, fits all SCF closures (two per kit) SCF-KT-6CBL Add-a-Cable Kit for two drop cables in 6-in end cap



A LANscape® Solutions Product



CORNING



notes |

A LANscape® Solutions Product

Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA 800-743-2675 • FAX: 828-901-5973 • International: +1-828-901-5000 • www.corning.com/cablesystems

Corning Cable Systems reserves the right to improve, enhance and modify the features and specifications of Corning Cable Systems products without prior notification. LANscape is a registered trademark of Corning Cable Systems Brands, Inc. All other trademarks are the properties of their respective owners. Corning Cable Systems is ISO 9001 certified. © 2005, 2009 Corning Cable Systems. All rights reserved. Published in the USA. LAN-347-EN / October 2009



