

Product Specifications



37 mm Double Back Box (M14D)

Material ID: 999901704

M14D Double Back Box



CHARACTERISTICS

Dimensions

Depth	8.89 mm 0.35 in
Height	85.85 mm 3.38 in
Weight	0.08 kg 0.18 lb
Width	145.80 mm 5.74 in

General Specifications

Color	White
Mount Type	Flush
Total Ports, quantity	4
Product Type	Faceplate: UK
Package, quantity	1

Mechanical Specifications

Material Type	High-impact, flame retardant, UL-rated 94 V-0, thermoplastic
---------------	--