

# Product Specifications



## M2000A 1U Blank Panel (Angled)

Material ID: 760091512

M2000 U/UTP 1U Blank Panel, angled

- Picture shown with CommScope Information Outlets installed. Information Outlets sold separately.

## CHARACTERISTICS

### Dimensions

Depth	30.48 mm   1.20 in
Height	44.45 mm   1.75 in
Width	482.60 mm   19.00 in

### Electrical Specifications

ANSI/TIA Category	3   5   5e   6   6A
-------------------	---------------------

### Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	cUL   UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

### General Specifications

Brand	CommScope®
Product Type	Cable manager   Label   Panel, modular
Total Ports, quantity	24
Color	Black
Package, quantity	1
Rack Type	EIA 19 in
Rack Units	1

### Mechanical Specifications

Material Type	High-impact, flame retardant, thermoplastic   Powder-coated steel
---------------	---

### Regulatory Compliance/Certifications

#### Agency

RoHS 2002/95/EC

#### Classification

Compliant

# Product Specifications

M2000A 1U Blank Panel (Angled) - Material ID: 760091512



ISO 9001:2000

Compliant

