

# Product Specifications



## CAT 3 (50) Port Panel

Material ID: 760060905

Category 3 U/UTP High Density Voice Patch Panel, 50 port



## CHARACTERISTICS

### Dimensions

Depth	139.70 mm   5.50 in
Height	44.45 mm   1.75 in
Width	482.60 mm   19.00 in

### Electrical Specifications

ANSI/TIA Category	5e
Current Rating	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1000 Vac @ 60 Hz

### Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
-----------------------	--------------------------------------

### General Specifications

Brand	SYSTIMAX®
Cable Type	U/UTP (unshielded)
Product Type	Panel
Total Ports, quantity	50
Color	Black
Package, quantity	1
Rack Type	EIA 19 in
Rack Units	1

### Mechanical Specifications

Rear Termination Contact Plating	Gold over nickel
Rear Termination Type	IDC

### Regulatory Compliance/Certifications

# Product Specifications

CAT 3 (50) Port Panel - Material ID: 760060905



## Agency

RoHS 2002/95/EC  
ISO 9001:2000

## Classification

Compliant  
Compliant

