Product Specifications

M18930-246

Material ID: 106720196

Surface Mount Modular Faceplate, ivory

CHARACTERISTICS

Dimensions

Depth	35.05 mm | 1.38 in
Height	80.01 mm | 3.15 in
Weight	0.06 kg | 0.12 lb
Width	65.02 mm | 2.56 in

General Specifications

Color	Ivory
Mount Type	Surface
Total Ports, quantity	2
Product Type	German modular faceplate
Application	Used with M-Series high density modules
Package, quantity	1

Mechanical Specifications

Material Type	High-impact, flame retardant, UL-rated 94 V-0, thermoplastic

SYSTIMAX® SOLUTIONS
www.commscope.com

©2010 CommScope, Inc. All rights reserved.
All trademarks identified by ® or ™ are registered trademarks or trademarks, respectively, of CommScope.
All specifications are subject to change. See www.commscope.com for the most current information.