

# Product Specifications



## iP-RACK-MGR-PLUS


Material ID: 760024588

iPatch® Rack Manager Plus

This product will be discontinued on: **12/31/2010**

### Replaced By:

360-iP-PANEL-MGR      SYSTIMAX 360™ iPatch® Panel Manager



## CHARACTERISTICS

### Dimensions

Depth	45.72 mm   1.80 in
Height	88.90 mm   3.50 in
Weight	0.82 kg   1.80 lb
Width	482.60 mm   19.00 in

### Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	Austel   CE   CSA   UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

### General Specifications

Brand	iPatch®   SYSTIMAX®
Product Type	Infrastructure control system
Color	Black
Package, quantity	1

### Mechanical Specifications

Material Type	ABS   Polycarbonate
---------------	---------------------

### Regulatory Compliance/Certifications

**SYSTIMAX®**  
**SOLUTIONS**  
[www.commscope.com](http://www.commscope.com)

©2010 CommScope, Inc. All rights reserved.  
All trademarks identified by ® or ™ are registered trademarks or trademarks, respectively, of CommScope.  
All specifications are subject to change. See [www.commscope.com](http://www.commscope.com) for the most current information.

page 1 of 2  
9/29/2010

# Product Specifications

iPRACK-MGR-PLUS - Material ID: 760024588



---

**Agency**

RoHS 2002/95/EC  
ISO 9001:2000

**Classification**

Compliant  
Compliant

