

Product Specifications



iP-PTF-24-LC-TS

Material ID: 760038547

iPatch® Pre-Terminated TeraSPEED® Intelligent Fiber Shelf, LC 24 port duplex

This product will be discontinued on: **12/31/2010**

Replaced By:

360-iP-INSTA-LC-4TS SYSTIMAX 360™ iPatch® G2 Fiber Shelf with InstaPATCH 360 TeraSPEED Modules



CHARACTERISTICS

Dimensions

Depth	323.85 mm 12.75 in
Height	44.45 mm 1.75 in
Weight	3.18 kg 7.00 lb
Width	482.60 mm 19.00 in

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	Austel CE CSA UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Brand	iPatch® SYSTIMAX®
Product Type	Intelligent fiber shelf, preterminated
Color	Black
Includes	Four #12-24 mounting screws Instruction sheet Shelf
Interface	LC
Package, quantity	1
Shelf Movement	Sliding
Total Ports, quantity	24

SYSTIMAX®
SOLUTIONS
www.commscope.com

©2010 CommScope, Inc. All rights reserved.
All trademarks identified by ® or ™ are registered trademarks or trademarks, respectively, of CommScope.
All specifications are subject to change. See www.commscope.com for the most current information.

page 1 of 2
9/29/2010

Product Specifications

iP-PTF-24-LC-TS - Material ID: 760038547



Mechanical Specifications

Fiber Type	TeraSPEED®, zero water peak single-mode fiber
Material Type	ABS Polycarbonate

Regulatory Compliance/Certifications

Agency

RoHS 2002/95/EC
ISO 9001:2000

Classification

Compliant
Compliant

