

Product Specifications



360-iP-G2-1 U-LC-FX

Material ID: 760105163

SYSTIMAX 360™ iPatch® G2 LC Fiber Shelf, fixed



CHARACTERISTICS

Dimensions

Depth	323.85 mm 12.75 in
Height	44.45 mm 1.75 in
Weight	1.81 kg 4.00 lb
Width	482.60 mm 19.00 in

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	Austel CE CSA UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Brand	iPatch® SYSTIMAX 360™ SYSTIMAX®
Product Type	Intelligent fiber shelf
Body Style	Duplex
Color	Black
Interface	LC
Package, quantity	1
Shelf Movement	Fixed
Total Ports, quantity	24

Mechanical Specifications

Fiber Type	LazrSPEED® 150, 50 µm multimode fiber LazrSPEED® 300, 50 µm multimode fiber LazrSPEED® 550, 50 µm multimode fiber OptiSPEED®, 62.5 µm multimode fiber TeraSPEED®, zero water peak single-mode fiber
Material Type	ABS Polycarbonate

Regulatory Compliance/Certifications

SYSTIMAX®
SOLUTIONS
www.commscope.com

©2010 CommScope, Inc. All rights reserved.
All trademarks identified by ® or ™ are registered trademarks or trademarks, respectively, of CommScope.
All specifications are subject to change. See www.commscope.com for the most current information.

page 1 of 2
9/29/2010

Product Specifications

360iP-G2-1U-LC-FX - Material ID: 760105163



Agency

RoHS 2002/95/EC
ISO 9001:2000

Classification

Compliant
Compliant

