

# Product Specifications



360GS10E-L-WH

Material ID: CPCSSZ2-08

GigaSPEED® X10D 360GS10E Solid Low Smoke Zero Halogen Cordage Modular Patch Cord, White Jacket



## CHARACTERISTICS

### Dimensions

Cord Length, maximum	100 ft   30 m
Cord Length, minimum	1 m   3 ft

### Electrical Specifications

ANSI/TIA Category	6A
dc Resistance, maximum	0.30 ohm
Safety Voltage Rating	300 V

### Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cETL   ETL

### General Specifications

Cable Type	U/UTP (unshielded)
Interface, connector A	RJ45 plug
Interface, connector B	RJ45 plug
Jacket Color	White
Brand	GigaSPEED® X10D   SYSTIMAX®
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Package, quantity	1
Pairs, quantity	4

### Mechanical Specifications

Conductor Type	Solid
Material Type	Copper alloy   Polycarbonate

# Product Specifications



360GS10E-LWH - Material ID: CPCSSZ2-08

Outlet/Module Contact Plating Gold over nickel  
Plug Insertion Life, minimum 750 times  
Plug Retention Force, minimum 133 N | 30 lbf  
Wiring T568B

## Wiring Diagram

	Connector A	Connector B
Position 1	White/Orange	White/Orange
Position 2	Orange	Orange
Position 3	Lt. Green	Lt. Green
Position 4	Blue	Blue
Position 5	Lt. Blue	Lt. Blue
Position 6	Green	Green
Position 7	Lt. Brown	Lt. Brown
Position 8	Brown	Brown

## Regulatory Compliance/Certifications

### Agency

RoHS 2002/95/EC  
ISO 9001:2000

### Classification

Compliant  
Compliant



## INCLUDED PRODUCTS

**3095B WH 4/24 RVAR** (Product Component—not orderable)

GigaSPEED® X10D 3095B Category 6A U/UTP Cable, non-plenum, white jacket, 4 pair count, variable length, reel