

# Product Specifications



## VP360T-360GS10E-L-DG

Material ID: CPCFSZ2-03

GigaSPEED® X10D VisiPatch® 360 to 360GS10E 4-pair Low Smoke Zero Halogen Solid Hybrid Patch Cord T, Dark Gray Jacket



## CHARACTERISTICS

### Dimensions

---

Cord Length, maximum	30 m   100 ft
Cord Length, minimum	2 m   7 ft

### Electrical Specifications

---

ANSI/TIA Category	6A
dc Resistance, maximum	0.30 ohm

### Environmental Specifications

---

Environmental Space	Low Smoke Zero Halogen (LSZH)
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cETL   ETL

### General Specifications

---

Interface, connector A	VisiPatch® 360
Interface, connector B	RJ45 plug
Product Type	Cord
Brand	SYSTIMAX®   VisiPatch® 360
Cable Type	U/UTP (unshielded)
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Jacket Color	Dark gray
Package, quantity	1
Pairs, quantity	4

# Product Specifications

VP360T-360GS10E-L-DG - Material ID: CPCFSZ2-03



## Mechanical Specifications

Conductor Type	Solid
Material Type	Copper alloy   Polycarbonate
Outlet/Module Contact Plating	Gold over nickel
Plug Insertion Life, minimum	200 times
Plug Retention Force, minimum	44 N   10 lbf
Wiring	T568B

## Wiring Diagram

	Connector A	Connector B
Position 1	Blue	White/Orange
Position 2	Lt. Blue	Orange
Position 3	Orange	Lt. Green
Position 4	White/Orange	Blue
Position 5	Green	Lt. Blue
Position 6	Lt. Green	Green
Position 7	Brown	Lt. Brown
Position 8	Lt. Brown	Brown

## Regulatory Compliance/Certifications

### Agency

RoHS 2002/95/EC  
ISO 9001:2000

### Classification

Compliant  
Compliant

