

# Product Specifications



110P8GS-DG

Material ID: CPC8812-03

GigaSPEED® 110GS to 110GS 4 Pair Patch Cord, Dark Gray Jacket



## CHARACTERISTICS

### Dimensions

---

Cord Length, maximum	30 m   100 ft
Cord Length, minimum	1 m   1 ft

### Electrical Specifications

---

ANSI/TIA Category	6
dc Resistance, maximum	0.30 ohm

### Environmental Specifications

---

Environmental Space	Non-plenum
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cETL   ETL

### General Specifications

---

Interface, connector A	110 plug
Interface, connector B	110 plug
Product Type	Cord
Cable Type	U/UTP (unshielded)
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Jacket Color	Dark gray
Package, quantity	1
Pairs, quantity	4

# Product Specifications



110P8GS-DG - Material ID: CPC8812-03

## Mechanical Specifications

Conductor Type	Stranded
Material Type	Copper alloy   Polycarbonate
Outlet/Module Contact Plating	Gold over nickel
Plug Insertion Life, minimum	200 times
Plug Retention Force, minimum	44 N   10 lbf
Wiring	110

## Wiring Diagram

	Connector A	Connector B
Position 1	Lt. Blue	Lt. Blue
Position 2	Blue	Blue
Position 3	White/Orange	White/Orange
Position 4	Orange	Orange
Position 5	Lt. Green	Lt. Green
Position 6	Green	Green
Position 7	Lt. Brown	Lt. Brown
Position 8	Brown	Brown

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2002/95/EC  
ISO 9001:2000

**Classification**  
Compliant  
Compliant



## INCLUDED PRODUCTS

**1074E DG 4/24 RVAR** (Product Component—not orderable)  
GigaSPEED® XL 1074E Category 6 U/UTP Cable, non-plenum, dark gray jacket, 4 pair count, variable length, reel