

# Product Specifications



120P4PS-DG

Material ID: CPC8658-03

110 to D8PS 2-pair Hybrid Patch Cord (120 version), Dark Gray Jacket

## CHARACTERISTICS

### Dimensions

---

Cord Length, maximum	30 m   100 ft
Cord Length, minimum	1 m   1 ft

### Electrical Specifications

---

ANSI/TIA Category	5e
dc Resistance, maximum	0.30 ohm

### Environmental Specifications

---

Environmental Space	Non-plenum
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cETL   ETL

### General Specifications

---

Interface, connector A	110 plug
Interface, connector B	RJ45 plug
Product Type	Cord
Cable Type	U/UTP (unshielded)
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Jacket Color	Dark gray
Package, quantity	1
Pairs, quantity	2

### Mechanical Specifications

---

Conductor Type	Stranded
Material Type	Copper alloy   Polycarbonate
Outlet/Module Contact Plating	Gold over nickel
Plug Insertion Life, minimum	200 times
Plug Retention Force, minimum	44 N   10 lbf
Wiring	120P4

# Product Specifications

120P4PS-DG - Material ID: CPC8658-03



## Wiring Diagram

	Connector A	Connector B
Position 1	Lt. Blue	Lt. Blue
Position 2	Blue	Blue
Position 3	White/Orange	White/Orange
Position 4	Orange	
Position 5		
Position 6		Orange
Position 7		
Position 8		

## Regulatory Compliance/Certifications

### Agency

RoHS 2002/95/EC  
ISO 9001:2000

### Classification

Compliant  
Compliant



## INCLUDED PRODUCTS

### **1074C DG 2/24 RVAR** (Product Component—not orderable)

GigaSPEED® XL 1074C Category 5e U/UTP Cable, non-plenum, dark gray jacket, 2 pair count, variable length, reel

### **5EJ2 GRAY BULK REEL** (Product Component—not orderable)

DataPipe® 5EJ2 Category 5e U/UTP Cable, non-plenum, gray jacket, 2 pair count, bulk length, reel