

Product Specifications



VP119-P2PS-DG

Material ID: CPC5662-03

VisiPatch® to PowerSUM D8PS 1 Pair Hybrid Patch Cord, Dark Gray Jacket



CHARACTERISTICS

Dimensions

Cord Length, maximum	30 m 100 ft
Cord Length, minimum	1 m 1 ft

Electrical Specifications

ANSI/TIA Category	5e
dc Resistance, maximum	0.30 ohm

Environmental Specifications

Environmental Space	Non-plenum
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cETL ETL

General Specifications

Interface, connector A	VisiPatch®
Interface, connector B	RJ45 plug
Product Type	Cord
Brand	SYSTIMAX® VisiPatch®
Cable Type	U/UTP (unshielded)
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Jacket Color	Dark gray

Product Specifications



VP119P2PS-DG - Material ID: CPC5662-03

Package, quantity 1
Pairs, quantity 1

Mechanical Specifications

Conductor Type Stranded
Material Type Copper alloy | Polycarbonate
Outlet/Module Contact Plating Gold over nickel
Plug Insertion Life, minimum 200 times
Plug Retention Force, minimum 18 N | 4 lbf
Wiring VisiPatch®

Wiring Diagram

	Connector A	Connector B
Position 1	Lt. Blue	
Position 2	Blue	
Position 3		
Position 4		Blue
Position 5		Lt. Blue
Position 6		
Position 7		
Position 8		

Regulatory Compliance/Certifications

Agency
RoHS 2002/95/EC
ISO 9001:2000

Classification
Compliant
Compliant



INCLUDED PRODUCTS

1074C DG 1/24 RVAR (Product Component—not orderable)
GigaSPEED® XL 1074C Category 5e U/UTP Cable, non-plenum, dark gray jacket, 1 pair count, variable length, reel

Product Specifications

VP119-P2PS-DG - Material ID: CPC5662-03



5EJ1 GRAY BULK REEL (Product Component—not orderable)

DataPipe® 5EJ1 Category 5e U/UTP Cable, non-plenum, gray jacket, 1 pair count, bulk length, reel
