

Product Specifications



GS8E-MGS400(BK)-S-DG

Material ID: CPC3282-13

GigaSPEED® XL GS8E to MGS400 on 1071 Solid Cable Zone Extension Cord, Dark Gray Jacket, Black Information Outlet



CHARACTERISTICS

Dimensions

Cord Length, maximum	100 m 300 ft
Cord Length, minimum	1 m 1 ft

Electrical Specifications

ANSI/TIA Category	6
dc Resistance, maximum	0.30 ohm
Safety Voltage Rating	300 V

Environmental Specifications

Environmental Space	Non-plenum
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cETL ETL

General Specifications

Cable Type	U/UTP (unshielded)
Interface, connector A	RJ45 plug
Interface, connector B	Information outlet
Jacket Color	Dark gray
Brand	GigaSPEED® XL SYSTIMAX®
Information Outlet Color	Black
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard

Product Specifications



GS8E-MGS400(BK)-S-DG - Material ID: CPC3282-13

Package, quantity 1
Pairs, quantity 4

Mechanical Specifications

Conductor Type Solid
Material Type Copper alloy | Polycarbonate
Outlet/Module Contact Plating Gold over nickel
Plug Insertion Life, minimum 750 times
Plug Retention Force, minimum 133 N | 30 lbf
Wiring T568B

Wiring Diagram

	Connector A	Connector B
Position 1	White/Orange	White/Orange
Position 2	Orange	Orange
Position 3	Lt. Green	Lt. Green
Position 4	Blue	Blue
Position 5	Lt. Blue	Lt. Blue
Position 6	Green	Green
Position 7	Lt. Brown	Lt. Brown
Position 8	Brown	Brown

Regulatory Compliance/Certifications

Agency

RoHS 2002/95/EC
ISO 9001:2000

Classification

Compliant
Compliant



INCLUDED PRODUCTS



MGS400-003

GigaSPEED® XL MGS400 Series Category 6 U/UTP Information Outlet , black

SYSTIMAX®
SOLUTIONS
www.commscope.com

©2010 CommScope, Inc. All rights reserved.
All trademarks identified by ® or ™ are registered trademarks or trademarks, respectively, of CommScope.
All specifications are subject to change. See www.commscope.com for the most current information.

page 2 of 3
10/1/2010

Product Specifications

GS8E-MGS400(BK)-S-DG - Material ID: CPC3282-13



1071E DG 4/23 RVAR (Product Component—not orderable)

GigaSPEED® XL 1071E ETL Verified Category 6 U/UTP Cable, non-plenum, dark gray jacket, 4 pair count, variable length, reel
