

Product Specifications



FBMSCUC11-EX

OptiSPEED® SC to Unconnectorized 0.9 mm Pigtail, SBJ, Riser, Slate Jacket

CHARACTERISTICS

Construction Materials

Fiber Type	OptiSPEED®, 62.5 µm multimode fiber
Total Fibers, quantity	1
Jacket Color	Slate

Dimensions

Cord Length, maximum	999 ft 999 m
Cord Length, minimum	1 ft 1 m
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

Environmental Specifications

Environmental Space	Riser
Operating Temperature	0 °C to +70 °C (+32 °F to +158 °F)

General Specifications

Interface, connector A	SC
Interface Feature, connector A	Standard
Construction Type	Pigtail
Interface, connector B	Unterminated

Mechanical Specifications

Cable Retention Strength, maximum	3.00 lb @ 90 ° 6.00 lb @ 0 °
-----------------------------------	---------------------------------

Regulatory Compliance/Certifications

Agency

RoHS 2002/95/EC
ISO 9001:2000

Classification

Compliant
Compliant



Product Specifications

FBMSCUC11-EX



INCLUDED PRODUCTS



N-001-RF-6F-F09SL

0.9 mm Low Smoke Zero Halogen Reinforced Buffered Fiber Cable

- **CS-6F-TB** (Product Component—not orderable)
OptiSPEED® OM1 Multimode Fiber



5403 001A MRSL

0.9 mm Low Smoke Zero Halogen Reinforced Buffered Fiber Cable

- **CS-6F-TB** (Product Component—not orderable)
OptiSPEED® OM1 Multimode Fiber