

Product Specifications



FBWSCUC11-JX

TeraSPEED® SC to Unconnectorized 0.9 mm SBJ Pigtail, Riser, Yellow Jacket

CHARACTERISTICS

Construction Materials

Fiber Type	TeraSPEED®, zero water peak single-mode fiber
Total Fibers, quantity	1
Jacket Color	Yellow

Dimensions

Cord Length, maximum	999 ft 999 m
Cord Length, minimum	1 ft 1 m
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

Environmental Specifications

Environmental Space	Riser
Operating Temperature	0 °C to +70 °C (+32 °F to +158 °F)

General Specifications

Interface, connector A	SC
Interface Feature, connector A	Standard
Construction Type	Pigtail
Interface, connector B	Unterminated

Mechanical Specifications

Cable Retention Strength, maximum	3.00 lb @ 90 ° 6.00 lb @ 0 °
-----------------------------------	---------------------------------

Regulatory Compliance/Certifications

Agency

RoHS 2002/95/EC
ISO 9001:2000

Classification

Compliant
Compliant



SYSTIMAX®
SOLUTIONS
www.commscope.com

©2010 CommScope, Inc. All rights reserved.
All trademarks identified by ® or ™ are registered trademarks or trademarks, respectively, of CommScope.
All specifications are subject to change. See www.commscope.com for the most current information.

page 1 of 2
10/7/2010

Product Specifications

FBWSCUC11jX



INCLUDED PRODUCTS



N-001-RF-8W-F09YL

0.9 mm Low Smoke Zero Halogen Reinforced Buffered Fiber Cable

- **CS-8W-TB** (Product Component—not orderable)
TeraSPEED® Singlemode Fiber



5403 001A WRYL

0.9 mm Low Smoke Zero Halogen Reinforced Buffered Fiber Cable

- **CS-8W-TB** (Product Component—not orderable)
TeraSPEED® Singlemode Fiber