

Product Specifications



FFXLCLC42-MX

LazrSPEED® 550 LC to LC Fiber Patch Cord, 1.6 mm Duplex, LSZH, Aqua Jacket



CHARACTERISTICS

Construction Materials

Fiber Type	LazrSPEED® 550, 50 µm multimode fiber
Jacket Color	Aqua
Total Fibers, quantity	2

Dimensions

Cord Length, maximum	999 ft 999 m
Cord Length, minimum	1 ft 1 m
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Operating Temperature	0 °C to +70 °C (+32 °F to +158 °F)

General Specifications

Construction Type	Duplex patch cord
Interface, connector A	LC
Interface Feature, connector A	Standard
Interface, connector B	LC
Interface Feature, connector B	Standard
Ordering Note	Not available in the United States or Canada

Mechanical Specifications



©2010 CommScope, Inc. All rights reserved.
All trademarks identified by ® or ™ are registered trademarks or trademarks, respectively, of CommScope.
All specifications are subject to change. See www.commscope.com for the most current information.

Product Specifications

FFXLCLC42-MX



Cable Retention Strength, maximum 4.40 lb @ 90 °
11.24 lb @ 0 °

Regulatory Compliance/Certifications

Agency

RoHS 2002/95/EC
ISO 9001:2000

Classification

Compliant
Compliant



INCLUDED PRODUCTS

460125198 (Product Component—not orderable)
Pre-Radiused LC Connector duplex for 1.6 mm Fiber, multimode
