

# Product Specifications



FJHMPMPAL-MB

LazrSPEED®150 MPO Female to MPO Female 96-Fiber InstaPATCH® Plus Distribution Trunk Cable, LSZH, Aqua Jacket

## CHARACTERISTICS

### Construction Materials

Fiber Type	LazrSPEED® 150, 50 µm multimode fiber
Jacket Color	Aqua
Total Fibers, quantity	96

### Dimensions

Breakout Length	Standard
Cord Length, maximum	999 ft   999 m
Cord Length, minimum	10 ft   3 m
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters   Minimum length may vary based on cable configuration

### Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Operating Temperature	0 °C to +70 °C (+32 °F to +158 °F)

### General Specifications

Construction Type	InstaPATCH® Plus trunk/extension/cross-connect
Interface, connector A	MPO Female
Interface Feature, connector A	Standard
Interface, connector B	MPO Female
Interface Feature, connector B	Standard
Cable Glands	Included
Pulling Grips, quantity	0
Ordering Note	Not available in the United States or Canada

### Mechanical Specifications

Cable Retention Strength, maximum	4.40 lb @ 90 ° 11.24 lb @ 0 °
-----------------------------------	----------------------------------

### Regulatory Compliance/Certifications

**Agency**  
RoHS 2002/95/EC  
ISO 9001:2000

**Classification**  
Compliant  
Compliant

# Product Specifications

FJHMPMPAL-MB



## INCLUDED PRODUCTS



**N-096-MP-5M-F12AQ** (Product Component—not orderable)

Low Smoke Zero Halogen Riser MPO Trunk Cable, 96 fiber multi-unit with 12 fiber subunits

- **CS-5M-MP** (Product Component—not orderable)

LazrSPEED® 150 OM2+ Multimode Fiber

---

**860366210** (Product Component—not orderable)

LazrSPEED® Low Loss MPO Female 12 Fiber Connector, aqua

---