

Product Specifications



UNC6-L-GY-3F

Material ID: CC0122952/1

Uniprise Category 6 U/UTP Patch Cord, RJ45 to RJ45, 4-pair, Low Smoke Zero Halogen, gray jacket, 3 feet



CHARACTERISTICS

Dimensions

Cord Length	3 ft
-------------	------

Electrical Specifications

ANSI/TIA Category	6
dc Resistance, maximum	0.30 ohm
Safety Voltage Rating	300 V

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cETL ETL

General Specifications

Cable Type	U/UTP (unshielded)
Interface, connector A	RJ45 plug
Interface, connector B	RJ45 plug
Jacket Color	Gray
Brand	Uniprise®
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Package, quantity	1
Pairs, quantity	4

Mechanical Specifications

Conductor Type	Solid
Material Type	Copper alloy Polycarbonate
Outlet/Module Contact Plating	Gold over nickel
Plug Insertion Life, minimum	750 times



©2011 CommScope, Inc. All rights reserved.
All trademarks identified by ® or ™ are registered trademarks or trademarks, respectively, of CommScope.
All specifications are subject to change. See www.commscope.com for the most current information.

page 1 of 2
2/21/2011

Product Specifications

UNC6-L-GY-3F - Material ID: CC0122952/1



Plug Retention Force, minimum 133 N | 30 lbf
Wiring T568B

Regulatory Compliance/Certifications

Agency

RoHS 2002/95/EC
ISO 9001:2008

Classification

Compliant
Designed, manufactured and/or distributed under this quality management system



INCLUDED PRODUCTS

UNC6ZH-i GRAY BULK REEL (Product Component—not orderable)

Uniprise UNC6ZH-i Category 6 U/UTP Cable, low smoke zero halogen, gray jacket, 4 pair count, bulk length, reel
