

Product Specifications



UNC6-L-GY-5F

Material ID: CC0122960/1

Uniprise Category 6 U/UTP Patch Cord, RJ45 to RJ45, 4-pair, Low Smoke Zero Halogen, gray jacket, 5 feet



CHARACTERISTICS

Dimensions

Cord Length 5 ft

Electrical Specifications

ANSI/TIA Category 6
dc Resistance, maximum 0.30 ohm
Safety Voltage Rating 300 V

Environmental Specifications

Environmental Space Low Smoke Zero Halogen (LSZH)
Flammability Rating UL 94 V-0
Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard cETL | ETL

General Specifications

Cable Type U/UTP (unshielded)
Interface, connector A RJ45 plug
Interface, connector B RJ45 plug
Jacket Color Gray
Brand Uniprise®
Interface Feature, connector A Standard
Interface Feature, connector B Standard
Package, quantity 1
Pairs, quantity 4

Mechanical Specifications

Conductor Type Solid
Material Type Copper alloy | Polycarbonate
Outlet/Module Contact Plating Gold over nickel
Plug Insertion Life, minimum 750 times



©2011 CommScope, Inc. All rights reserved.
All trademarks identified by ® or ™ are registered trademarks or trademarks, respectively, of CommScope.
All specifications are subject to change. See www.commscope.com for the most current information.

Product Specifications



UNC6-L-GY-5F - Material ID: CC0122960/1

Plug Retention Force, minimum 133 N | 30 lbf
Wiring T568B

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



INCLUDED PRODUCTS

UNC6ZH-i GRAY BULK REEL (Product Component—not orderable)

Uniprise UNC6ZH-i Category 6 U/UTP Cable, low smoke zero halogen, gray jacket, 4 pair count, bulk length, reel
