

Ortronics

OR-40300547

TracJack Faceplate, three-port (single gang), plastic, Fog White - OR-40300547



Ortronics Single Gang Plastic Faceplates accept front-loading TracJack modules and include two snap-in label fields



FEATURES

- **Low profile design:** Blends with most environments.
- **Recessed label fields:** Supports TIA/EIA 606 standard.
- **Easily accepts snap-in TracJacks:** Easily field configured.
- **Front-load module approach:** Improves access for future work.
- **Textured finish:** Hides future scuffs.
- **Oval mounting holes:** Assists proper alignment

Specifications

APP INSTALL INFO

Mounting Hardware Included: #6-32*25 mm Screw, Binding Head (2 ea)

DIMENSION INFO

Ortronics

OR-40300547

Height Metric: 114.3 mm

Width Metric: 69.85 mm

Depth Metric: 7.62 mm

Height U S: 4.5"

GENERAL INFO

Category Performance Application: Single gang

Number Of Ports: 3-port

Color: Fog White

Footprint: TracJack

LISTING AGENCY INFO

UL E131600

BUY AMERICAN ACT COMPLIANCE

Country of Origin: TAIWAN

Buy American Act Status: Trade Agreement Act Compliant