

Ortronics

OR-FC04U-C

4U rack mount fiber cabinet for combination patch/splice applications - OR-FC04U-C



The 4U (7.0" high) fiber cabinet for patch/splice applications is optimized for integration with the Mighty Mo 6 rack system (OR-MM6710, OR-MM6810 & Seismic Rack OR-MM6710S) with 10.5" channel depth. Each fiber cabinet accepts up to 12 adapter panels and 16 splice trays.



FEATURES

- 19" (483 mm) deep cabinet chassis
- Large cable entry port in rear of cabinet
- Fiber tray slides forward
- Fiber tray slides rearward
- Optimized hook/loop lances embedded in fiber tray
- Comes with patented snap-in fiber management clips
- Large patch cord exit ports at front of cabinet
- Adapter panel face positioned to optimize patch cord management

BENEFITS

- Provides more room for internal fiber management and is optimized for use with Mighty Mo 6 10.5" deep rack system
- Unrestricted access for backbone cable entry, excellent for use with pre-terminated cables

Ortronics

OR-FC04U-C

Provides superior access for termination of optical fibers, internal fiber routing and patch cord management

Unique feature that provides additional access to improve backbone cable management and internal fiber routing

Lances positioned for optimal internal fiber management

Clips ensure fiber bend radius compliance and snap into strategically positioned receptacles for a secure installation and optimum fiber protection

Provide maximum clearance/space for management of fiber patch cords in high density installations

Positioning designed for best possible patch cord exit when installed in Mighty Mo 6 rack system

Specifications

DIMENSION INFO

Rack Units: 4

Height Metric: 177.80 mm

Width Metric: 482.60 mm

Depth Metric: 485.77 mm

Height U S: 7 in

BUY AMERICAN ACT COMPLIANCE

Country of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant