

MM10 Server Rack - OR-MM107SVR



MM10 Server Rack, 7', black.



FEATURES

- Works with all of the Mighty Mo 6 and 10 racks and cable management
- Choice of vertical management can be mounted front or rear
- The mounting rails adjust from 12.5" to 30", independent of the structural members
- Built-in top trough with waterfalls
- Rack includes two packages of hook and loop D-style straps and 50 #12-24 cage nuts and screws
- Static capacity: 1,500 lbs. (evenly distributed) with center base mounted at the end of the rack or under the adjustable rear rails for greater support

BENEFITS

- Provides a unified, streamlined look

Ortronics

OR-MM107SVR

- A solution for every application; vertical cable management cage with individual rack unit fingers and hinged door, vertical cage with hinged access latches, and cable management rings
- Allows the rails to be adjusted after the rack is installed
- Gives bend radius control and cable routing
- Do not have to purchase as separate items; money saving

Specifications

DIMENSION INFO

Rack Units: 45

Height Metric: 2.2 m

Width Metric: 603 mm

Depth Metric: 889 mm

Height U S: 85.25"

Capacity Weight U S: Static capacity 1500 lbs. (see features below)

TECHNICAL INFO

Patent No: Patent pending

CONSTRUCTION INFO

Component1: Frame - Material1: Aluminum, Finish_Plating1: Black Powdercoat

BUY AMERICAN ACT COMPLIANCE

Country of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant