

Ortronics

OR-MM6716

MM6 Cable Management Racks, 16.25 channel depth, 7' - OR-MM6716



MM6 Cable Management Racks, 16.25 channel depth, 7', black



FEATURES

- High density racking solution
- Choice of vertical management
- Patented channel construction
- Built-in top trough with waterfalls
- Open channels top and bottom
- EIA hole pattern front and rear of channel
- Can be assembled as a 19" or 23" rack
- Footprint 23.75" W x 21.5" D (when assembled as a 19" rack and rear base angle turned in)
- Speed nuts included
- Rack includes hardware kit, two packages of hook and loop D-style straps and 50 #12-24 equipment mounting screws

BENEFITS

Ortronics

OR-MM6716

- 45 rack units front and rear
- A solution for every application; vertical cable management cage with individual rack unit fingers and hinged door, vertical cage with hinged access latches, and cable management rings
- Protects and conceals your horizontal cabling like no other rack
- Gives bend radius control and cable routing
- Allows floor and ceiling access for horizontal distribution cables
- Supports equipment shelves and heavy electronics while power strips and other accessories can be mounted to the rear rail without using additional rack space
- No additional hardware required; no need to stock two sizes of racks
- Stays within a 2' square footprint
- Increases speed and ease of assembly, while adding extra strength to your rack--Speednut eliminates the need for a second wrench
- Do not have to purchase as separate items; money saving

Specifications**DIMENSION INFO**

Rack Units: 45

Height Metric: 2.2 m

Width Metric: 603 mm

Depth Metric: 667 mm

Height U S: 86"

TECHNICAL INFO

Patent No: D360,189

BUY AMERICAN ACT COMPLIANCE

Country of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant