

Clarity 5E 12-port, Category 5e mini patch, hinged mounting, 10" x 2.5" - OR-PMP5E12H



Clarity 5E 12-port mini patch panel is component compliant to EIA/TIA Category 5e performance requirements. Its high density design on hinged wall mounting provides access to wire terminations while maximizing wall space in small or confined locations. The panel measures 10" x 2.5". Jacks are grouped in six-port modules. Part of the Clarity 5E link and channel solution that provides significant installed performance headroom.



FEATURES

- **ETL verified to TIA Category 5e component spec:** Elevated component performance.
- **Center tuned to Clarity 5E patch cords:** More transparent mated union.
- **Universal wiring:** Supports T568A and T568B installs.
- **Easy lace 110 termination:** Saves installation time.
- **Supplied rear cable management:** Supports good cabling practice.
- **High density design:** Maximizes rack utilization.
- **RoHS compliant:** Lead free.

Specifications

DIMENSION INFO

Height Metric: 254 mm

Width Metric: 63.5 mm

Ortronics

OR-PMP5E12H

Cable Diameter Range: 22-26 AWG

Height U S: 10 in

GENERAL INFO

Mod Jack Wiring: Universal T568A/B

Number Of Ports: 12

TECHNICAL INFO

Performance Rating: Category 5e

Category Rating: Category 5e

CONSTRUCTION INFO

Component1: Panel - Material1: 0.125" Aluminum, Finish_Plating1: Painted black texture with green silkscreen

Component4: Array of eight modular dual reactance contacts - Material4: Beryllium copper, Finish_Plating4: Nickel plating and a minimum of 50 micro inches of selective gold plating in contact area

Component5: IDC contacts (low noise) - Material5: Phosphor Bronze, Finish_Plating5: Nickel plating with tin over plate

LISTING AGENCY INFO

FCC

UL E131600

BUY AMERICAN ACT COMPLIANCE

Country of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant