


Ortronics

OR-OFP-STD12MB

## 6 ST-Duplex (12 fibers) multimode adapters with phosphor-bronze alignment sleeves - OR-OFP-STD12MB

Ortronics fiber adapter panel allows for flexibility and expansion with an industry accepted style. The adapter panel snaps in for installation and can be removed easily for future changes. The adapter panel is silkscreened for easy port identification



### FEATURES

- **Standard adapter panel is front removable:** Ideal for simple moves, adds, and changes.
- **Uses plunger/grommet fastener:** Holds adapter panels securely in place.

### Specifications

#### APP INSTALL INFO

Mounting Hardware Included: Yes

#### DIMENSION INFO

Height Metric: 30

Width Metric: 130

Ortronics

OR-OFP-STD12MB

Height U S: 1.19

**GENERAL INFO**

Number Of Ports: 6

Typical Applications: Multimode

**TECHNICAL INFO**

Fiber Capacity: 12

**BUY AMERICAN ACT COMPLIANCE**

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant