

### SNCA-PS24-4E

An external power supply with one 4 Amp 24V AC fused output. Polycarbonate IP66 rated enclosure suitable for outdoor use.



Key feature: Ideal for powering 24V AC housings and the camera. This power supply must be used when a camera is in a housing of any type (dome or fixed).

This power supply is to be used with housings and camera combinations only. Please use either SNCA-PS12-1 or SNCA-PS24-1 for other cameras

SNCA-HFIXED

SNCA-HRZ25

SNCA-HRZ30

SNCA-HRX550/EXT

SNCA-HRX550/EXT/W

SNCA-HRX550/EXT/R

SNCA-HRX550/INT

SNCA-HRZ50/EXT

SNCA-HRZ50/EXT/W

SNCA-HRZ50/EXT/R

SNCA-HRZ50/INT

Supply Voltage: 230V AC 50Hz

Input connection: Internal connection, no cable supplied

Current Consumption: Approx. 100W

Colour: White

Size in mm (W x H x D): 118 x 200 x 70

Weight in Kg: 2.1

Packed Size in mm (W x H x D): 124 x 208 x 76

Packed Weight (Kg): 2.2

Case Material: Powder coated Mild Steel

Operating Temperature: -10°C to +40°C

Storage Temperature: -20°C to +50°C

Environmental Class: 2 (indoor use only)

MTBF: 65,000 hours

CE approved: Yes

Output Voltage: 24V AC

Output Current: 4A (fused)

Output connection: Internal connection, no cable supplied

Tamper Switch: No

## Compatible Products

### Housings



#### SNCA-HRX550-INT

Indoor dome camera housing



#### SNCA-HRX550EXT-R

Outdoor vandal resistant dome camera housing



#### SNCA-HRX550-PRE

Outdoor Pressurized dome camera housing



#### SNCA-HRX550EXT/W

Outdoor wireless dome camera housing



#### SNCA-HRX550EXT

Outdoor dome camera housing



#### SNCA-HRZ50-EXT

Outdoor dome camera housing



**SNCA-HRZ50-INT**

Outdoor dome camera housing



**SNCA-HRZ50/EXT/W**

Outdoor Wireless dome camera housing



**SNCA-HRZ50/EXT/R**

Outdoor dome camera housing