

4 Inch Dome

Indoor/Outdoor 4" Vandal Dome

DOME 4-I

DOME 4-O



MegaVideo® Housing

Excellent protection for the entire MegaVideo® line of Arecont Vision cameras. Combining this 4" dome with the superior imaging of an AV camera provides the perfect solution for environments in which cameras need to be less noticeable, or require additional protection from the elements.

Arecont Vision Advantages:

Superior Solution for Various Environments

- Indoor or outdoor applications

Excellent Enclosure Protection

- IP66 Rating

Vandal Resistant

- Tough, high-impact polycarbonate construction with a heavy duty enclosure for harsh environments

Full View in All Directions

- Camera can be rotated a full 360° horizontally and 0-90° vertically

Compatibility

- Designed to House the Entire Line of MegaVideo® Cameras

Easy Installation

- Easy installation and superior design, perfect for indoor or outdoor applications

Other key features:

- Heater option (DOME 4-O): - 25°C (-13°F)
- Surface Mounting, 2 Axis Camera Positioning and more

Designed to House the Entire Line of Color and Day/Night Megapixel Cameras:

AV1300, AV2100, AV3100, AV3130, AV5100

Learn more about our products at www.arecontvision.com

Model Numbers:

Dome 4-I - Indoor/Outdoor Vandal Resistant Dome

Dome 4-O - Outdoor Vandal Resistant Dome with Heater

Mechanical

- Housing material:
Aluminum
- Dome Cover Protection:
Vandal resistant polycarbonate
- Dome Cover Diameter:
4.5 inch (114.3 mm)
- Back Plate Diameter:
6.30 inch (160 mm)
- Housing Height:
4.90 inch (125 mm)
- Dome Cover Height:
2.80 inch (70 mm)
- Housing Diameter:
6.30 inch (160 mm)
- Weight w/o camera:
2.2lbs(1kg)
- Security:
Tamper proof screws

Environmental

- Operating Temperature:
0°C (32 °F) to 50°C (122 °F)
- Heater option (DOME 4-O): - 25°C (-13°F)
- Humidity:
0 to 95 % relative, non-condensing
- Enclosure Protection:
IP66 Rating

Compatible Cameras

AV1300M, AV1300DN,
AV1305, AV1305DN,
AV2100M, AV2100DN,
AV2105, AV2105DN,
AV3130 M, AV3130DN,
AV3100M, AV3100DN,
AV3105, AV3105DN,
AV5100, AVAV5100DN,
AV5105, AV5105DN

Optional Heater (Available in Dome 4-O Only)

12VDC/24VAC

Power consumption: 0.6 Watts

