

5 Inch Dome

Indoor 5" Recessed Dome

DOME 5-I

Arecont Vision
megapixel technology...
beyond imagination



MegaVideo® Housing

Excellent protection for the entire MegaVideo® line of Arecont Vision cameras. Combining this 5" dome with the superior imaging of an AV camera provides the perfect solution for environments in which cameras need to be less noticeable, or require additional protection from the elements.

Arecont Vision Advantages:

Exceptional View

- Outstanding observation with excellent color sensitivity and high resolution

Excellent Enclosure Protection

- Indoor only

Full View in All Directions

- Camera can be rotated a full 360° horizontally and 0-90° vertically

Compatibility

- Designed to house the entire line of MegaVideo® cameras

Easy Installation

- Superior design for indoor applications

Other key features:

- Recessed mounting, 3 Axis camera positioning and more

Designed to House the Entire Line of Color and Day/Night Megapixel Cameras:

AV1300, AV2100, AV3100, AV3130, AV5100

Learn more about our products at www.arecontvision.com

www.arecontvision.com avsales@arecontvision.com 818.937.0700 877.CAMERA.8

Model Numbers:

Dome 5-I - Indoor Recessed Dome

Mechanical

- Bubble Diameter - 5 inch (127 mm)
- Dust Protection cover box:
 - Length: 8 inch (203 mm)
 - Width: 4.5 inch (114 mm)
 - Height: 3 inch (76 mm)
- Housing Height - 3 inch (76 mm)
- Dome Height - 2.80 inch (70 mm)
- Housing Diameter - 7 inch (178 mm)
- Dome Cover Height - 2.80 inch (70mm)

Environmental

- Operating Temperature - 0C (32 °F) to 50C (122 °F)
- Humidity - 0 to 95% relative, non-condensing
- Enclosure Protection - Indoor Only

Compatible Cameras

AV1300M, AV1300DN,
AV1305, AV1305DN,
AV2100M, AV2100DN,
AV2105, AV2105DN,
AV3130 M, AV3130DN,
AV3100M, AV3100DN,
AV3105, AV3105DN,
AV5100, AVAV5100DN,
AV5105, AV5105DN

