

MAIN FEATURES

For indoor and outdoor installations

Constructed from aluminium, painted with epoxy powder

DESCRIPTION

PTAC

Wall mount for PTH300 and PTH355P Pan & Tilt motors, constructed from aluminium, painted with epoxypolyester powder RAL9002. It is suitable for mounting on any kind of surface.

PTBC

Wall bracket for PTH900 Pan & Tilt motor. Constructed from die-cast aluminium and painted with epoxypolyester powder RAL9002, it can be perfectly combined with PTCC1 pole adapter and WCWGC corner adapter.

PTPC

Top of pole adapter plate for PTH900, PTH300 and PTH355P Pan & Tilt motors. Constructed from 3mm-thick sheet steel and painted with epoxypolyester powder RAL9002, it ensures a firm fixing of the Pan & Tilt motor.

PTDC

Ceiling bracket for PTH900, PTH300 and PTH355P Pan & Tilt motors. Constructed from aluminium painted with epoxypolyester powder RAL9002, it ensures a firm fixing of the Pan & Tilt motor.

WFWBTA

Column bracket suitable for PTH900, PTH300 and PTH355P Pan & Tilt motors, constructed from aluminium and furnace painted with epoxypolyester powder RAL9002. It can be used with PTBC, WFWCA and PTAC brackets.



PTAC



PTPC



PTDC



WFWBTA

205

			_		
Ī	3	Ę	9		
ľ		۲	Э		
			á		
			_		
Ę	7	ς	J		
	3	Ĉ	3		
۹	è	ŝ	į.		
d	i	ï	5		
			3		
P	4	٦	4		
ľ	7	ľ	7		
			4		

BRACKETS AND P&T								
P&T	Wall		Ceiling	Top Pole	Column			
Bracket	PTAC	PTBC	PTDC	PTPC	WFWBTA			
PTH300	•		•	•	•			
PTH355P	•		•	•	•			
PTH900		•		•	•			

TECHNICAL DATA

GENERAL

Constructed from die-cast aluminium

Epoxypolyester powder painting, RAL9002 colour

Constructed from steel (only PTPC)

MECHANICAL

PTAC

Wall mounting or on modular adapters

Load rating: 35kg (77lb)

Length: 360mm (14.1in)

PTBC

Wall mounting

Load rating: 50kg (110lb)

Length: 458mm (18in)

PTPC

Top of pole mounting

Load rating: 50kg (110lb)

Length: 105mm (4.1in)

Pole dimensions: Ø 80 - 120mm (3.1-4.7in)

PTDC

Ceiling mounting

Load rating: 50kg (110lb)

Length: 320mm (12.6in)

WFWBTA


Parapet mounting

Load rating: 50kg (110lb)


Height: 185mm (7.2in)

ENVIRONMENT

Indoor / Outdoor



200 = 141 = = 141 = 200 = 100 = 320




WFWBTA

PTDC

PTPC

mm 1:10

PTAC



mm 1:10

PACKAGE							
Code	Unit weight		Package weight		Package dimensions (WxHxL)		Master carton
	kg	lb	kg	lb	cm	in	unit
PTAC	0.7	1.5	0.9	2.0	13.5x13.5x45.0	5.3x5.3x17.7	12
PTBC	2.2	4.9	2.5	5.5	20.5x15.5x49.0	8.0x6.1x19.3	8
PTPC	1.9	4.2	2.1	4.6	14.5x15.0x27.0	5.6x5.9x10.6	15
PTDC	0.9	2.0	1.2	2.6	22.0x22.0x35.5	8.6x8.6x14.0	-
WFWBTA	0.8	1.8	1.0	2.2	14.3x15.0x27.0	5.6x5.9x10.6	15

207

P&T BRACKETS